

830-003 Size #12 Pneumatic Pin Contact




Special
Purpose

Size #12 Pneumatic Contacts



Contact Type	For Use With	Tube I.D.	Part Number
Pin	D38999 All Series, Series 80	.094 (2.38)	830-003



Stainless steel pneumatic contacts attach to 3/32 inch (2.38) diameter tubing. Contacts snap into size #12 connector cavities. These pneumatic contacts are rated for 100 PSI maximum air pressure. No installation tool is required. Remove contacts with plastic extraction tool 809-132.

Material and Finish

Body and Cap: stainless steel, passivated
O-ring: fluorosilicone
Washers: PTFE

Specifications

Contact may be used for air pressures up to 100±10% PSIG
Fits #12 socket contact cavities.

Notes

High pressure pneumatic contacts available. Consult factory for more information.
For Series 79, use 857-010 and 857-011.