



610-014 E-Nut Backshell for Connector Designators A, F, L, S & H

CONNECTOR DESIGNATOR:

A	MIL-DTL-5015, -26482 Series II, and -83723 Series I and III
F	MIL-DTL-38999 Series I, II
L	MIL-DTL-38999 Series 1.5 (JN1003)
H	MIL-DTL-38999 Series III and IV
S	PATT 105 / 603 / 608

A



NOTES

1. Metric dimensions (mm) are in parenthesis and are for reference only.
2. See Table I in Intro for front-end dimensional details.

TABLE II: DASH NUMBER

Shell Size		B Max	C Diameter Ref.
A, F, L, S	H		
03	--	.702 (17.3)	.270 (6.9)
08	09	.640 (16.3)	.270 (6.9)
10	11	.765 (19.4)	.375 (9.5)
12	13	.890 (22.6)	.511 (13.0)
14	15	1.015 (25.8)	.585 (14.9)
16	17	1.140 (29.0)	.710 (18.0)
18	19	1.265 (32.1)	.789 (20.0)
20	21	1.390 (35.3)	.914 (23.2)
22	23	1.454 (36.9)	1.039 (26.4)
24	25	1.594 (40.5)	1.154 (29.3)
61	--	1.640 (41.7)	1.194 (30.3)

TABLE III: FINISH

Symbol	Finish Description
XB	No Plating - Black Color
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. 1000 Hour Grey™
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel