



610-014 E-Nut Backshell for Connector Designators A, F, L, S & H

A

| CONNECTOR DESIGNATOR: | |
|-----------------------|---|
| A | MIL-DTL-5015, -26482 Series II, and -83723 Series I and III |
| F | MIL-DTL-38999 Series I, II |
| L | MIL-DTL-38999 Series 1.5 (JN1003) |
| H | MIL-DTL-38999 Series III and IV |
| S | PATT 105 / 603 / 608 |



| NOTES | |
|-------|---|
| 1. | Metric dimensions (mm) are in parenthesis and are for reference only. |
| 2. | See Table I in Intro for front-end dimensional details. |

| Shell Size | | B Max | C Diameter Ref. |
|------------|----|--------------|-----------------|
| A, F, L, S | H | | |
| 03 | -- | .702 (17.3) | .270 (6.9) |
| 08 | 09 | .640 (16.3) | .270 (6.9) |
| 10 | 11 | .765 (19.4) | .375 (9.5) |
| 12 | 13 | .890 (22.6) | .511 (13.0) |
| 14 | 15 | 1.015 (25.8) | .585 (14.9) |
| 16 | 17 | 1.140 (29.0) | .710 (18.0) |
| 18 | 19 | 1.265 (32.1) | .789 (20.0) |
| 20 | 21 | 1.390 (35.3) | .914 (23.2) |
| 22 | 23 | 1.454 (36.9) | 1.039 (26.4) |
| 24 | 25 | 1.594 (40.5) | 1.154 (29.3) |
| 61 | -- | 1.640 (41.7) | 1.194 (30.3) |

| Symbol | Finish Description |
|--------|--|
| XB | No Plating - Black Color |
| XM | 2000 Hour Corrosion Resistant Electroless Nickel |
| XMT | 2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. <i>1000 Hour Grey™</i> |
| XW | 2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel |