



667-104 Composite Receptacle Cover for MIL-DTL-38999 Series III Connectors with Anti-Rotation Device




TABLE II	
Symbol	Finish Description
XB	No Plating - Black Color (Non-Conductive Finish)
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. 1000 Hour Grey™
XO	No Plating - Brown Color (Non-Conductive Finish)
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel

B




TABLE I: CONNECTOR SHELL SIZE		
Shell Size	A Thread	B Max
09	.6250-0.1P-0.3L-TS	.906
11	.7500-0.1P-0.3L-TS	1.102
13	.8750-0.1P-0.3L-TS	1.220
15	1.0000 -0.1P-0.3L-TS	1.260
17	1.1875 -0.1P-0.3L-TS	1.457
19	1.2500 -0.1P-0.3L-TS	1.535
21	1.3750 -0.1P-0.3L-TS	1.654
23	1.5000 -0.1P-0.3L-TS	1.772
25	1.6250 -0.1P-0.3L-TS	1.929

Metric dimensions (mm) are in parentheses and are for reference only.