

SERIES 79 MICRO-CRIMP RECTANGULAR CONNECTORS

Backshells and Accessories



Band-Master ATS® Banding Straps

Band-Master ATS®




Terminate cable braid shield with stainless steel **Band-Master ATS®** bands. Install band with hand tool or bench-mounted pneumatic tool. Bands are available in three widths: **Standard** (.24 inch), **Micro** (.12 inch) and **Nano** (.075 inch). **Slim Standard** and **Micro Slim** bands have reduced thickness for weight reduction. Hardened steel **Micro-Max** bands have double the tensile strength of standard Micro bands. Available flat or pre-coiled, bands are 304 series stainless steel, passivated.

For more information on the Band-Master ATS shield termination system, including instruction manuals and calibration details:

<https://www.glenair.com/bandmaster/>

BAND STRAP PART NUMBERS										
Band Type	A Length		Part Number		Fits up to Dia.		B Width		C Thickness	
	in	mm	Flat	Pre-coiled	in	mm	in	mm	in	mm
Standard	9	228	601-005	601-006	1.00	25.4	.24	6.1	.02	0.51
	14	356	601-040	601-041	1.80	45.7	.24	6.1	.02	0.51
	18	457	601-049	601-050	2.50	63.5	.24	6.1	.02	0.51
Slim Standard	9	228	601-570	601-571	.94	23.9	.24	6.1	.01	0.25
	14	356	604-572	601-573	1.80	45.7	.24	6.1	.01	0.25
Micro	5	127	601-024	601-025	.50	12.7	.12	3.0	.015	0.38
	8	203	601-060	601-061	.88	22.4	.12	3.0	.015	0.38
	14	356	601-064	601-065	1.88	47.7	.12	3.0	.015	0.38
Micro Slim	8	203	601-600	601-601	.88	22.4	.12	3.0	.01	0.25
	14	356	601-602	601-603	1.88	47.7	.12	3.0	.01	0.25
Micro-Max	8	203	601-700	601-701	.88	22.4	.12	3.0	.015	0.38
	14	356	601-702	601-703	1.80	45.7	.12	3.0	.015	0.38
Nano	6	152	601-500	601-501	.60	15.2	.075	1.9	.009	0.23
	9	228	601-504	601-505	.94	23.9	.075	1.9	.009	0.23
	14	356	601-508	601-509	1.80	45.7	.075	1.9	.009	0.23



BANDING TOOLS



HAND BANDING TOOL

Glenair Band-Master ATS® tools are equipped with a built-in counter to ensure required recalibration is performed in accordance with military and commercial aerospace requirements.



PNEUMATIC BANDING TOOL

High volume bench tool provides fast, consistent band termination with minimal operator fatigue.

Band Type	Hand Tool Part Number	Pneumatic Tool Part Number
Standard	601-100	601-106
Slim Standard	601-109	601-110
Micro	601-101	601-107
Micro Slim	601-122	601-123
Micro-Max	601-129	601-130
Nano	601-108	601-118