

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 791 Scoop-Proof



Series 791 Product Selection Guide

Series 791 Contents

- Series 791 Features B-3
- Insert Arrangements B-4
- Specifications B-5
- Series 791 for Space Flight B-6
- Series 791 Material and Finish Options B-7
- Mod-555 Keying Option B-8
- Series 791 Panel Cutouts B-52

**Contacts
and Tools**

Page E-1

**Backshells
and
Accessories**

Page F-1

**PCB
Footprints**

Page G-1

**Cable
Receptacles**

Pin Contacts

Cable Receptacle
Backshell Groove



791-001 Page B-9

Cable Receptacle
Banding Platform



791-002 Page B-11

Cable Plugs

Socket Contacts

Cable Plug
Backshell Groove



791-003 Page B-13

Cable Plug
Banding Platform




791-004 Page B-15

**Panel
Receptacles**


Pin Contacts

Panel Receptacle




791-019 Page B-17

Panel Receptacle
Float Mount



791-017 Page B-19

Panel Receptacle
Hermetic




791-069 Page B-21

Panel Plugs

Socket Contacts

Panel Plug



791-020 Page B-24

Panel Plug
Float Mount



791-018 Page B-26

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 791 Scoop-Proof



Series 791 Product Selection Guide

SERIES 791 SCOOP-PROOF


PCB Connectors

PCB Receptacle
Straight PC Tails



791-013 Page B-28

PCB Receptacle
90° PC Tails



791-032 Page B-30

PCB Plug
Straight PC Tails



791-014 Page B-32


PCB Plug
90° PC Tails



791-016 Page B-34


Panel Mount PCB Connectors

Panel Mount PCB Recep
Straight PC Tails



791-021 Page B-36

Panel Mount PCB Recep
90° PC Tails



791-011 Page B-38

Panel Mount PCB Plug
Straight PC Tails



791-033 Page B-40

Panel Mount PCB Plug
90° PC Tails



791-012 Page B-42


Filtered Connectors

Cable Receptacle
Solder Cup Pin Contacts




240-791-001 Page B-44

Cable Plug
Solder Cup Socket Contacts



240-791-003 Page B-46

Panel Receptacle
Solder Cup Pin Contacts



240-791-005 Page B-48

Panel Plug
Solder Cup Socket Contacts



240-791-007 Page B-50