

Series 79 Mil-Grade Miniature Rectangular Connectors FA07364 Breakout Assembly

PRIZM[®] MT and MT Elite[®]

HOW TO ORDER	
Sample Part Number	FA07364 -06 -17 ME -B4 -50 -L -1 -036 L
Basic Number	Series 79 MT Ferrule Fiber Optic Cable Assembly
A Connector Type	-06 = Sr. 79 Plug 183-003 (used with male MT ferrule) -07 = Sr. 79 Receptacle 183-003 (used with female MT ferrule) -S7 = Sr. 79 Receptacle 183-003 with EMI gasket (used with female MT ferrule)
B Connector Type	-06 = Sr. 79 Plug 183-003 (used with male MT ferrule) -07 = Sr. 79 Receptacle 183-003 (used with female MT ferrule) -S7 = Sr. 79 Receptacle 183-003 with EMI gasket (used with female MT ferrule) -12 = ST Connector -13 = FC Connector -14 = SC Connector -15 = GC Connector -16 = LC Connector -17 = MT Connector (male) -18 = MT Connector (female) -19 = MTP Connector (male) -20 = MTP Connector (female)
Material / Finish (-06, -07, -S7)	ME = Al Alloy / Electroless Nickel MT = Al Alloy / Nickel PTFE ZR = Al Alloy / Zinc Nickel, Black NF = Al Alloy / Cadmium, O.D. Z1 = Stainless Steel / Passivate
Fiber Qty. / Type	-B2 = 12 bare ribbon fibers -B4 = 24 bare ribbon fibers -R2 = 12 round ribbon fibers -R4 = 24 round ribbon fibers
Fiber Size	-09 = 9.3/125 Singlemode -50 = 50/125 Multimode -62 = 62.5/125 Multimode
Mounting Hardware (A Connector)	<u>Plug</u> -L = Hex head jackscrew, non-removable -B = Thru-hole <u>Receptacle</u> -X = Rear-panel jackpost, .031" thickness -W = Rear-panel jackpost, .041" thickness -V = Rear-panel jackpost, .062" thickness -T = Rear-panel jackpost, .094" thickness -R = for .080" panel thickness
Mounting Hardware (B Connector, applies to Sr. 79 only)	<u>Series 79 Plug</u> -L = Hex head jackscrew, non-removable -B = Thru-hole -K = Slotted Head Jackscrew, non-removable <u>Series 79 Receptacle</u> -X = Rear-panel jackpost, .031" thickness -W = Rear-panel jackpost, .041" thickness -V = Rear-panel jackpost, .062" thickness -T = Rear-panel jackpost, .094" thickness Omit = if not Sr. 79 connector
Banding Platform (A Connector)	-1 = without banding platform -2 = with banding platform
Banding Platform (B Connector, applies to Sr. 79 only)	-1 = without banding platform -2 = with banding platform Omit if not Sr. 79 connector
Length	In inches (e.g. -0036 = 36 inches)
Protective Cover	L = supplied less covers Omit = supplied with covers

Unless indicated, no polarization key will be used for plug and receptacle Sr. 79 connectors.

Part numbering is for reference purposes only. A unique Glenair part number will be assigned to your cable order. Please consult factory for additional custom cable offerings.

