

SERIES 28

HiPer-D® Accessories

Shorting Plug Assembly

289-053




Ordering Information					
Sample Part Number	289-053P	1H15	ME	N	S
Basic Part Number	289-053P HiPer-D Shorting Plug with Pin Contacts				
Shell Size/Insert Arrangements	See Contact Arrangement tables				
Shell Finish	ME - Electroless Nickel Over Aluminum MT - Nickel Fluorocarbon Over Aluminum Z1 - Passivated Stainless ZM - Electroless Nickel Over Stainless JF - Yellow Chromate Over Cadmium				
Grounding Option	G - EMI/Grounding N - None N - None (Thru Hole) P - Female Jackpost L - Low Profile Jackscrew K - Extended Jackscrew S - Low Profile Jackpost T - Extended Jackpost				
Hardware Options					

NOTES

1. Assembly identified with Glenair's name and part number, space permitting.
2. Material/finish
Plug assembly - see plating in p/n development
Hardware - CRES/passivated
3. See 280-018 for connector details.
4. HIPOT/DWV requirement: 5 ohms

Dimensions					
Shell Size	Insert Pattern	A Max		B Max	
		In.	mm	In.	mm
1	S9; H15	.894	22.71	.550	13.97
2	S15; H26	1.218	30.94	.550	13.97
3	S25; H44	1.760	44.70	.550	13.97
4	S37; H62	2.408	61.16	.550	13.97
5	S50; H78	2.297	58.34	.654	16.61
6	H104	2.422	61.52	.716	18.19



STANDARD AND HIGH DENSITY CONTACT ARRANGEMENTS (face view of pin connector)

