



A

Performance Specifications			
Electrical			
Description	Requirement		Procedure
Current Rating	<b>Contact Size</b>	<b>Max Current</b>	EIA-364-70 Method 1 IEC-60512-5 Test 9b
	8	40	
	20	7.5	
	22	5	
Shell-to-Shell Resistance (connectors with ground springs)	2.5 milli-volt drop maximum		EIA-364-83 IEC-60512-2-6 Electroless nickel plated connectors.
Shielding Effectiveness	<b>Frequency GHz</b>	<b>Min Attenuation (dB)</b>	EIA-364-66 IEC-60512-23-3 Pin Connector with Optional Grounding Spring, Electroless nickel plated shells
	0.1	100	
	0.4	90	
	0.8	85	
	1.0	80	
	3.0	55	
	6.0	40	
10.0	30		