

SERIES 80 Mighty Mouse connectors



Size 12 Coax Crimp Contacts For 50 and 75 Ohm Coax Cable


SIZE #12 COAXIAL CONTACTS




#12 Socket Contact

These #12 contacts accept 50 Ohm and 75 Ohm coaxial cable. Inner contact is rated at 1 amp, the outer contact 12 amps. DWV voltage rating is 1000 VAC RMS sea level, 250 Vac at 50,000 feet. Contacts are packaged individually and shipped unassembled with instruction sheet. One contact consists of outer contact, fluorocarbon dielectric, inner contact and shield crimp sleeve. Inner and outer contacts are gold-plated copper alloy. Approved to SAE AS39029. VSWR rating 1.5:1 maximum operating frequency range up to 700 MHz depending on cable selection. 5000 megOhm insulation resistance.

Туре	Cable Size	Part Number	Military Part Number	Color Band		
				1st	2nd	3rd
Pin	RG174, RG316, RG179	809-118	M39029/28-211	Red	Brown	Brown
Pin	RG180	809-119	M39029/28-409	Yellow	Black	White
Socket	RG174, RG316, RG179	809-120	M39029/27-210	Red	Brown	Black
Socket	RG180	809-121	M39029/27-402	Yellow	Black	Red





Contact Crimp and Removal Tools						
Description	Glenair P/N	Military P/N				
Inner Contact, Crimp Tool	809-015	M22520/2-01				
Inner Contact, Positioner	809-135	M22520/2-34				
Outer Contact, Crimp Tool	809-133	M22520/31-01				
Outer Contact, Positioner	859-134	M22520/31-02				
Installation Tool	N/A	M81969/8-09				
Removal Tool	859-049	M81969/8-10				