



SERIES 805 TRIPLE-START ACME THREAD Mighty Mouse Connectors and Cables



Panel Cutout Dimensions and Polarization

PANEL CUTOUT DIMENSIONS

Panel Cutout For Jam-Nut and Wall Mount Receptacles					
Shell Size	Square Flange			Jam-Nut	
	G Bsc	Ø H	Ø R	N Flat	Ø P
8	.660 (16.76)	.096 (2.44) .091 (2.31)	.515 (13.08)	.545 (13.84) .541 (13.74)	.572 (14.53) .567 (14.40)
9	.723 (18.36)		.578 (14.68)	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)
10	.785 (19.94)		.640 (16.26)	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)
11	.848 (21.54)		.703 (17.86)	.731 (18.57) .727 (18.47)	.760 (19.30) .755 (19.18)
12	.909 (23.09)		.765 (19.43)	.794 (20.17) .790 (20.07)	.822 (20.88) .817 (20.75)
13	.973 (24.71)		.828 (21.03)	.851 (21.62) .847 (21.51)	.885 (22.48) .881 (22.38)
15	1.058 (26.87)	.130 (3.30) .126 (3.20)	.953 (24.21)	.980 (24.89) .976 (24.79)	1.010 (25.65) 1.005 (25.53)
18	1.255 (31.88)		1.140 (28.96)	1.157 (29.39) 1.153 (29.29)	1.198 (30.43) 1.193 (30.30)
19	1.327 (33.71)		1.203 (30.56)	1.231 (31.27) 1.227 (31.17)	1.260 (32.00) 1.255 (31.88)
21	1.452 (36.88)		1.328 (33.73)	1.358 (34.49) 1.354 (34.39)	1.383 (35.13) 1.381 (35.08)
23	1.570 (39.88)		1.453 (36.91)	1.480 (37.59) 1.476 (37.49)	1.510 (38.35) 1.505 (38.23)

POLARIZATION

Plug Key Positions		
Position	A°	B°
Normal (A)	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

Receptacle Keyway Positions		
Position	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°