



SERIES 811 HIGH-DENSITY DOUBLE-START Mighty Mouse Connectors and Cables

Product Selection Guide



Series 811

Connector features and benefits, weight savings comparisons, connector weights, contact arrangement layouts, panel cut-out dimensions, and key/keyway positions and polarizations.

Page K-2



Series 811 HD Cable Plug Connector Pigtails

Factory terminated cable plugs with PTFE or Tefzel® insulated wire, backpotted with epoxy.

Page K-7



Series 811 HD In-Line Receptacle Connector Pigtails

Factory terminated in-line receptacles with PTFE or Tefzel® insulated wire, backpotted with epoxy.

Page K-8



Series 811 HD Wall Mount Receptacle Connector Pigtails

Factory terminated wall mount receptacles with PTFE or Tefzel® insulated wire, backpotted with epoxy.

Page K-9



Series 811 HD Jam-nut Receptacle Connector Pigtails

Factory terminated jam-nut receptacle connector pigtails with PTFE or Tefzel® insulated wire, backpotted with epoxy.

Page K-11



Series 811 HD Jam-nut Straight PCB Receptacles

Jam-nut mount straight PC tail receptacles with enhanced environmental sealing for open-faced immersion requirements.

Page K-13



Series 811 HD Box Mount Straight PCB Receptacles

Box mount PC tail receptacles with enhanced environmental sealing for open-faced immersion requirements.

Page K-14



Series 811 HD Harsh Environment Cordsets

Overmolded Series 811 cordsets withstand rugged abrasion, fluid and chemical exposure. Silver-coated stranded conductors with TFE insulation, tinned copper braided shielding and extruded polyurethane jacket.

Page K-16