

# ULTRAMINIATURE CIRCULAR Series 806 Mighty Mouse Mil-Aero Connectors



## Hex jam nuts for Mighty Mouse receptacles

Replacement hex jam-nut for series 806 jam-nut mount receptacles. Optional wire holes available where jam-nuts must be safety-wired to prevent loosening.



How To Order					
SAMPLE PART NUMBER		806-035	ME	10	W
Product	806-035 = Hex jam-nut for Series 806 Receptacles				
Finish	See material and finish table				
Shell Size	7 8 9 10 11 12 14 16 18 20 22 24				
Wire Holes	W = Ø .06 wire hole; omit for none				

Dimensions			
Shell Size	'A' Hex	'B' Thread	'C'
7	.76 (19.3)	M8 X 1.06h 0.100 R	.88 (22.4)
8	.82 (20.8)	M15 X 1.06h 0.100 R	.92 (23.4)
9	.86 (21.8)	M16 X 1.06h 0.100 R	.97 (24.6)
10	.94 (23.9)	M18 X 1.06h 0.100 R	1.06 (26.9)
11	.98 (24.9)	M19 X 1.06h 0.100 R	1.10 (27.9)
12	1.06 (26.9)	M21 X 1.06h 0.100 R	1.19 (30.2)
14	1.26 (32.0)	M24 X 1.06h 0.100 R	1.42 (36.1)
16	1.31 (33.3)	M27 X 1.06h 0.100 R	1.48 (37.6)
18	1.41 (35.8)	M30 X 1.06h 0.100 R	1.60 (40.6)
20	1.58 (40.1)	M34 X 1.06h 0.100 R	1.79 (45.5)
22	1.71 (43.4)	M37 X 1.06h 0.100 R	1.394 (35.4)
24	1.86 (47.2)	M41 X 1.06h 0.100 R	2.12 (53.8)

Material/Finish		
Code	Material	Finish
NF	Aluminum Alloy	CAD/O.D. OVER ELECTROLESS NICKEL
MT		NICKEL-PTFE
ME		ELECTROLESS NICKEL (96 HOUR SALT SPRAY)
ZR		ZINC NI, BLACK (TRI-VALENT CR)
Z1	Stainless Steel	PASSIVATE
ZL		ELECTRO-DEPOSITED NICKEL

