



Series 80 Mighty Mouse Standard and High-Speed Series Cordsets and Jumpers

Standard and High-Speed Cordsets

AVAILABLE FOR ALL MIGHTY MOUSE SERIES CONNECTORS

Harsh Environment Shielded Cordsets



Point-to-point cordsets with polyamide or high-temp rubber overmolding and shielded, jacketed cable for environmental applications

Ultraflexible Phantom Cordsets



Point-to-point cordsets with polyamide or high-temp rubber overmolding and flexible fabric overbraid for non-environmental applications

High Pressure AquaMouse Cordsets



Point-to-point cordsets with polyamide or high-temp rubber overmolding and shielded, jacketed cable for high-pressure applications

Mighty Mouse Cordsets for Ethernet and other high-speed data applications



Native Mighty Mouse to Mighty Mouse point-to-point cordsets with polyamide or high-temp rubber overmolding and shielded, jacketed cable for high-speed applications




Mighty Mouse to commercial USB point-to-point cordsets with polyamide or high-temp rubber overmolding and shielded, jacketed cable for Universal Serial Bus applications



Mighty Mouse to commercial RJ45 point-to-point cordsets with polyamide or high-temp rubber overmolding and shielded, jacketed cable for Cat 5 and Cat 6 Ethernet applications

Special application, point-to-point cordsets



Unique overmolding compounds, jacketing and overbraid materials available on a build-to-print basis



Incorporation of customer-supplied connectors, including audio frequency and non-standard power connectors



Ethernet jumpers incorporating Mighty Mouse connectors in place of non-rugged commercial connectors