



Rectangular I/O and Printed Circuit Board Connectors

GTB connector product selection guide
Featuring size #22 contacts and .100" contact spacing

STANDARD DENSITY

PRODUCT SELECTION GUIDE

Connector	Description	Page Number
	GTBB-ST - Straight PCB Vertical Mount Connector, Pin or Socket Contacts, without Mounting Ears	6
	GTBA-ST - Straight PCB Vertical Mount Connector, Socket Contacts, and Mounting Ears	8
	GTBB-SF - Straight PCB Vertical Mount Flex Terminated Connector, with Pin or Socket Contacts, without Mounting Ears	10
	GTBA-SF - Straight PCB Vertical Mount Flex Terminated Connector, with Socket Contacts, and Mounting Ears	12
	GTBB-SC - Straight PCB Vertical Mount Connector, with Solder Cup Terminated Pin or Socket Contacts, without Mounting Ears	14

Connector	Description	Page Number
	GTBA-SC - Straight PCB Vertical Mount Connector, with Solder Cup Terminated Socket Contacts, and Mounting Ears	16
	GTBA-RA - Right Angle PCB Connector, with Pin Contacts and Mounting Ears	18
GTB PCB Connector Hardware Options		20
GTBA-RA Right Angle PCB Layouts		23
GTBA-ST Straight and and GTBA-SF Straight Flex PCB Layouts		28

55302 GTB PART NUMBER OVERVIEW

Mounting Ears	Drawing	Description	Contact	Contact Arrangemnts
Connectors with mounting ears	GTBA-ST	PC Tail	Pin, Socket	(1 Bay) 10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, 70w
	GTBA-RA	Right Angle PC Tail	Pin	
	GTBA-SC	Solder Cup	Socket	
	GTBA-SF	Flex PC Tail	Socket	(2 Bay) 90, 100, 120
Connectors without mounting ears	GTBB-ST	PC Tail	Pin, Socket	10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, 70
	GTBB-SC	Solder Cup	Socket	
	GTBB-SF	Flex PC Tail	Socket	
	GTBB-CR	Crimp (non mil spec)	Pin, Socket	10, 14, 20, 24, 26, 30, 36, 40, 44, 50, 54, 56, 60, 66, 70

© 2026 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • MIL-DTL-55302 Catalog
Dimensions in Inches (millimeters) are subject to change without notice.