

MIL-QPL'D AND COMMERCIAL EQUIVALENT

NAVY CONNECTORS, TERMINI, ACCESSORIES AND TOOLS

RUGGEDIZED, ENVIRONMENTAL INTERCONNECT SOLUTIONS



Glenair offers a complete line of Navy connector solutions: From QPL'd MIL-PRF-28876 fiber optic connectors for today's high-speed ship-to-shore communications, to qualified MIL-DTL-28840 shipboard electrical connectors and accessories for ruggedized environmental shipboard interconnect systems, to precision tools for crimping and termination. The products are fully tooled and many are ready for immediate, same-day shipment.



GLENAIR, INC. • 1211 Air Way • Glendale, CA 91201-2497 • Tel: 818-247-6000 • Email: sales@glenair.com • www.glenair.com

U.S. Navy Approved Connectors and Accessories Index



Part/Config. Number	Page
180-040-03	C-6
180-040-04	C-8
180-040-06	C-10
180-040-13	C-6
180-040-14	C-8
180-040-16	C-10
180-040-23	C-7
180-040-24	C-9
180-040-26	C-11
180-040-33	C-7
180-040-34	C-9
180-040-36	C-11
181-039-1250C	B-1
181-039-1255C	B-1
181-039-1260C	B-1
181-039-1270C	B-1
181-039-1420C	B-1
181-040-1250C	B-2
181-040-1255C	B-2
181-040-1260C	B-2
181-040-1270C	B-2
181-040-1420C	B-2
181-051	B-3
181-057-125	B-14
181-057-126	B-14
181-075-125	B-14
181-075-126	B-14
182-012	B-4
182-013	B-5
182-014	B-6
182-015	B-7
182-035	B-8
240-288A	F-4
240-288J	F-8

Part/Config. Number	Page
240-288W	F-6
660-072	C-14
660-073	C-14
850-004	D-8
850-004-20-450	D-8
850-004-20-451	D-8
850-004-20-508	D-8
850-005	D-10
850-005-20-452	D-10
850-005-20-453	D-10
850-005-20-509	D-10
907-003	F-1
907-037	F-2
930-006	F-14, C-13
941-002	F-15
947-128	F-10
947-229	F-12
GAP-036	B-9
GCLT-H200	B-17
GCLT-HC250	B-17
GCLT-H160	B-17
GCLT-H125	B-17
GCLT-C125	B-17
GCLT-C250	B-17
GCLT-MPO	B-17
GCLT-MTC	B-17
GCLT-MTC-RE	B-17
M22520/34-01	D-3
M22520/34-02	D-3
M22520/35	D-3
M28840/1	E-1
M28840/2	E-2
M28840/3	E-3
M28840/4	E-4

Dimensions in Inches (millimeters) are subject to change without notice.



U.S. Navy Approved Connectors and Accessories Index

Part/Config. Number	Page
M28840/5	E-5
M28840/6	E-8
M28840/7	E-11
M28840/8	E-12
M28840/9	E-17
M28840/10	E-22
M28840/11	E-23
M28840/12	E-24
M28840/13	E-25
M28840/14	E-26
M28840/15	E-27
M28840/16	E-28
M28840/17	E-29
M28840/18	E-30
M28840/19	E-31
M28840/20	E-32
M28840/21	E-34
M28840/22	E-36
M28840/23	E-37
M28840/24	E-38, C-13
M28840/25	E-39
M28840/26	E-42
M28840/27	E-43
M28840/28	E-46
M28840/29	E-48
M28840/30	E-50
M28876/1	C-6
M28876/2	C-6
M28876/3	C-7
M28876/4	C-7
M28876/5	C-12
M28876/6	C-10
M28876/7	C-10
M28876/8	C-11

Part/Config. Number	Page
M28876/9	C-11
M28876/10	C-14
M28876/11	C-8
M28876/12	C-8
M28876/13	C-9
M28876/14	C-9
M28876/15	C-14
M29504/3-4038	B-3
M29504/14-4131C	B-1
M29504/14-4132C	B-1
M29504/14-4135C	B-1
M29504/14-4140C	B-1
M29504/14-4141C	B-1
M29504/15-4171C	B-2
M29504/15-4172C	B-2
M29504/15-4175C	B-2
M29504/15-4180C	B-2
M29504/15-4181C	B-2
M39029/83	D-8
M39029/83-450	D-8
M39029/83-451	D-8
M39029/83-508	D-8
M39029/84	D-10
M39029/84-452	D-10
M39029/84-453	D-10
M39029/84-509	D-10
M81969/33-01	D-3
M81969/33-02	D-3
M81969/34-01	D-3
TG69	F-17
TG70	F-16
TG82	F-17

Dimensions in Inches (millimeters) are subject to change without notice.