

SuperNine Series I Bayonet PowerPlay  
660-141 Receptacle Cover





**MATERIAL/FINISH**

- Hardware, rivet: CRES/passivate
- Sealant, rivet: two part epoxy
- Rope attachments: Per Attachment Rings Style Table

**NOTES**

- Max diameter over which mandrel will rotate freely shown in Attachment Ring Table.
- Length tolerance for sash chain (s) is ± one (1) link, for all other attachments ± .25.
- Knurling: mfr's option


**ATTACHMENT TYPE**



Symbol	Attachment
F	Wire Rope, Nylon Jacket with Terminal
G	.094 Dia Nylon Cord (Black) with Loop Ends
H	Wire Rope, Teflon Jacket with Terminal
N	Attachment Omitted
R	Wire Rope, PVC Jacket with Terminal
T	Wire Rope, No Jacket, with Terminal
K	Nylon Rope
S	#8 Sash Chain, CRES, Passivate

HOW TO ORDER						
<b>Sample Part Number</b>	<b>660-141</b>	<b>ME</b>	<b>17</b>	<b>R</b>	<b>6</b>	<b>-01</b>
<b>Basic Part Number</b>	<b>660-141 PowerPlay Receptacle Cover</b>					
<b>Material/Finish</b>	<b>ME</b> = Aluminum Alloy, Electroless Nickel <b>MT</b> = Aluminum Alloy, Nickel-PTFE <b>NF</b> = Aluminum Alloy, Cad/O. D. Over Electroless Nickel (1000 Hour Salt Spray) <b>TZ</b> = Aluminum Alloy, Tin Zinc <b>Z1</b> = Stainless, Passivate					
<b>Shell Size</b>	See Cover Dimensions Table					
<b>Attachment Type</b>	See Attachment Rings Style Table					
<b>Attachment Length</b>	In Inches					
<b>Ring Style Dash Number</b>	See Attachment Ring Table					

COVER DIMENSIONS	
Shell Size	G DIA Max
11	.984 (24.99)
13	1.157 (29.39)
15	1.280 (32.51)
17	1.406 (35.71)
19	1.516 (38.51)
21	1.642 (41.71)
23	1.768 (44.91)
25	1.890 (48.01)



ATTACHMENT RING							
Style A		Style B		Style C		Style D	
Dash Number	C Dia	Dash Number	D Dia	Dash Number	E Dia	Dash Number	F Dia
085	0.265 (6.73)	08	0.468 (11.89)	50	0.425 (10.80)	01	0.140 (3.56)
095	0.312 (7.92)	10	0.593 (15.06)	52	0.485 (12.32)	02	0.182 (4.62)
100	0.391 (9.93)	12	0.718 (18.24)	54	0.640 (16.26)	03	0.191 (4.85)
101	0.516 (13.11)	14	0.844 (21.44)	56	0.750 (19.05)	04	0.197 (5.00)
102	0.583 (14.81)	16	0.968 (24.59)	58	0.890 (22.61)	05	0.167 (4.24)
103	0.641 (16.28)	18	1.093 (27.76)	60	1.015 (25.78)	06	0.125 (3.18)
104	0.708 (17.98)	20	1.187 (30.15)	62	1.095 (27.81)	07	0.218 (5.54)
105	0.766 (19.46)	22	1.343 (34.11)	64	1.130 (28.70)	09	0.156 (3.96)
106	0.896 (22.76)	24	1.484 (37.69)	66	1.250 (31.75)	00	No Eyelet
107	1.016 (25.81)	28	1.687 (42.85)	68	1.350 (34.29)	<b>Style RL</b>	
108	1.141 (28.98)	32	1.968 (49.99)	70	1.375 (34.92)	 STYLE RL SEE DRAWING 677-048	
109	1.266 (32.16)	36	2.187 (55.55)	72	1.485 (37.72)		
110	1.391 (35.33)	40	2.406 (61.11)	74	1.625 (41.28)		
111	1.521 (38.63)	44	2.656 (67.46)	76	1.750 (44.45)		
112	1.641 (41.68)	48	3.031 (76.99)	78	1.875 (47.63)		
113	1.766 (44.86)			80	1.980 (50.29)		
114	1.891 (48.03)			82	2.060 (52.32)		
115	2.078 (52.78)			84	2.235 (56.77)		
116	2.406 (61.11)			86	2.310 (58.67)		
117	2.510 (63.75)			88	2.475 (62.87)		
				90	2.655 (67.44)		
				92	2.810 (71.37)		
				94	3.045 (77.34)		

SUPERNINE SERIES I POWERPLAY BAYONET