

962-025-086 BLUMARK RF COAX CABLE, CONNECTOR CONTACT, AND MULTI-PORT HOUSING COMPATIBILITY MATRIX



Pin Contact



Socket Contact

**Size 8 for use with
-086 cable**
18 GHz BMB interface
50 Ohm
Solder termination
Snap-in, rear release
pin and socket coax
contacts, spring-loaded.



962-025-086

BLUMARK
COAX CABLES **RF**

- 50 ohm size 086 (.104" jacket diameter, .020" conductor) 40 GHz max. bandwidth low-attenuation cable
- -65 to +150 °C rated operating temperature
- FEP jacket, PFA dielectric, solid SPC center conductor
- Double-shielded: Tape/braid shield layers with >90 dB shield effectiveness



Series 23 SuperNine
"Better than QPL" MIL-DTL-38999 Series III



Series 806 RF Mil-Aero
Micro miniature circular IAW D38999



Series 795 RF
High-performance multi-port rectangular

852-071-05 Pin	✓	✓	✓
852-070-05 Socket	✓		
852-152-05 Socket		✓	✓
G-LinkRF 852-157 Pin	✓	✓	✓
G-LinkRF 852-158 Socket	✓		
G-LinkRF 852-256 Socket		✓	✓