

660-109

Protective Cover for BNC Plug


BNC Plug Cover



TABLE 1 MATERIAL / FINISH

Aluminum	Stainless Steel
M Electroless Nickel	Z1 Passivate
NF Olive Drab Cadmium	ZM Nickel-plated
MT Nickel-PTFE	
ZR Black Zinc-Nickel	

TABLE 2 ATTACHMENT TYPE



D	 SST Bead Chain .125 (3.2) diameter, size 6, -65 to +200 °C
F	 Wire Rope, Blue Nylon Jacket 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C
G	 Black Nylon Rope Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C
H	 Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C
S	 Sash Chain #8 sash chain, stainless steel. Length tolerance is ± one link .280 (71)
T	 SST Wire Rope, No Jacket Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C
U	 SST Wire Rope, Black Polyurethane Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C

660-109 protective cover fits BNC plug connectors. Aluminum or stainless steel, with stainless steel fittings. Silicone gasket.

PART NUMBER

Base P/N	660-109	M	H	095	-4
Material/Finish	See Table 1				
Attachment Type	N No Attachment See Table 2 for Attachment Types				
Attachment Ring	Omit for Attachment Type N 00 No Ring See Table 3 for Attachment Ring Codes				
Attachment Length	Omit for Attachment Type N Length in One Inch Increments				

TABLE 3 ATTACHMENT RING

EYELET		
	Code	Eyelet I.D.
	06	.125 (3.2)
	01	.140 (3.6)
	02	.182 (4.6)
	04	.197 (5.0)
SOLID RING		
	Code	Ring I.D.
	095	.312 (7.9)
	100	.391 (9.9)
	101	.516 (13.1)
	102	.583 (14.8)
	103	.641 (16.3)
	104	.708 (18.0)
	105	.766 (19.5)
	106	.896 (22.2)
	107	1.016 (25.8)
SPLIT RING		
	Code	Ring I.D.
	52	.485 (12.3)
	54	.640 (16.3)
	56	.750 (19.1)
	58	.890 (22.6)
	60	1.015 (25.8)

