



Contact arrangements (pin face shown)




3-50

3X SIZE 20 CONTACT




7-50

7X SIZE 20 CONTACT




12-6

6X SIZE 20 CONTACT




12-50

12X SIZE 20 CONTACT




19-4

4X SIZE 12 CONTACT




19-7

7X SIZE 12 CONTACT




19-12

12 SIZE 16 CONTACT




19-50

19X SIZE 20 CONTACT




27-2

14X SIZE 16 CONTACT




27-3

2X SIZE 16 CONTACT
14X SIZE 20 CONTACT




27-5

19X SIZE 16 CONTACT




27-8

6X SIZE 16 CONTACT
4X SIZE 12 CONTACT



27-11


12X SIZE 20 CONTACT



27-50


27X SIZE 20 CONTACT

Contact arrangements (pin face shown)




37-2

24X SIZE 16 CONTACT




37-3

12X SIZE 12 CONTACT




37-50

37X SIZE 20 CONTACT



61-42

4X SIZE 16 CONTACT
29X SIZE 20 CONTACT
8X SIZE 12 CONTACTS



61-50

61X SIZE 20 CONTACT