



## Glenair Series ITS and ITS-RG MIL-DTL-5015 Type Reverse Bayonet Connectors Contact Arrangement Tables

**A**

Arrangement	Rating	Contact Number	Contact Size								
			4/0	0	4	8	12	16	18	20	
10SL-3	A	3							3		
10SL-4	A	2							2		
14S-1	A	3							3		
14S-2	I	4							4		
14S-5	I	5							5		
14S-6	I	6							6		
14S-7	A	3							3		
14S-9	A	2							2		
14S-07	I	7							7		
16S-1	A	7							7		
16S-4	D	2							2		
16S-5	A	3							3		
16S-8	A	5							5		
16-2	E	1					1				
16-7	A	3				1			2		
16-9	A	4					2	2			
16-10	A	3					3				
16-11	A	2					2				
16-12	A	1			1						
16-A10*	I	10								10	
18-1	I	10							10		
18-3	D	2					2				
18-4	D	4						4			
18-5	D	3					2	1			
18-6	D	1			1						
18-06	A	6					4	2			
18-7	B	1				1					
18-8	A	8					1	7			
18-9	I	7					2	5			
18-10	A	4					4				
18-10S MT	A	4					4				
18-11	A	5					5				
18-12	A	6						6			
18-13	A	4				1	3				
18-16	C	1					1				
18-19	A	10						10			
18-20	A	5						5			
18-22	D	3						3			
18-30 (18-20x110°)	A	5						5			
20-2	D	1		1							
20-3	D	3					3				
20-4	D	4					4				
20-6	D	3						3			
20-7	A	8						8			
20-8	I	6				2		4			
20-9	A	8					1	7			
20-11	I	13						13			
20-14	A	5				2	3				
20-15	A	7					7				
20-16	A	9					2	7			
20-17	A	6					5	1			
20-18	A	9					3	6			
20-19	A	3				3					
20-21	A	9					1	8			
20-22	A	6				3		3			
20-23	A	2				2					
20-24	A	4				2		2			
20-A24	A	4				2		2			
20-25 (20-11x100°)	I	13						13			
20-27	A	14						14			

Arrangement	Rating	Contact Number	Contact Size								
			4/0	0	4	8	12	16	18	20	
20-29	A	17								17	
20-30 (20-11x250°)	I	13								13	
20-33	A	11								11	
20-A8	I	8					2			6	
20-A9	A	9						9			
20-A48	I	19								19	
20-B8	A	8						4	4		
22-1	D	2					2				
22-2	D	3					3				
22-4	A	4					2	2			
22-5	D	6						2	4		
22-7	E	1		1							
22-9	E	3						3			
22-10	E	4							4		
22-11	B	2							2		
22-12	D	5					2		3		
22-14	A	19								19	
22-15	A	6						5	1		
22-17	A	9						1	8		
22-18	A	8								8	
22-19	A	14								14	
22-20	A	9								9	
22-21	A	3		1					2		
22-22	A	4					4				
22-23	A	8						8			
22-27	A	9					1		8		
22-28	A	7						7			
22-34	D	5						3	2		
22-82	A	10					2		8		
22-A10	A	10							10		
22-A37*	A	37									37
22-22S MT	A	4					4				
24-2	D	7						7			
24-3	A	7						2	5		
24-4	D	4					1		3		
24-5	A	16								16	
24-06	D	6						4	2		
24-6	A	8							8		
24-07	D	7							7		
24-7	A	16							2	14	
24-9	A	2					2				
24-10	A	7						7			
24-11	A	9						3	6		
24-12	A	5					2		3		
24-013	A	13							6	7	
24-19	A	12								12	
24-20	D	11							2	9	
24-22	D	4						4			
24-27	E	7								7	
24-28	I	24								24	
24-67	A	19							19		
24-A1	B	1					1				
24-A8	A	8						5	3		
24-A11	A	11						2		9	
24-A12	A	12					2			10	
24-A25	A	25								25	
24-A28	I	28								28	
24-A55*	I	55									55
24-G5	A	5						5			
28-1	A	9						3	6		
28-2	D	14							2	12	

\* Only Crimp Contact Version

# Glenair Series ITS and ITS-RG MIL-DTL-5015 Type Reverse Bayonet Connectors Contact Arrangement Tables



Arrangement	Rating	Contact Number	Contact Size							
			4/0	0	4	8	12	16	18	20
28-3	E	3				3				
28-6	D	3			3					
28-09	A	9			4			5		
28-9	D	12				6	6			
28-10	A	7		2	2	3				
28-11	A	22				4	18			
28-12	A	26					26			
28-13 (28-12x100*)	A	26					26			
28-15	A	35					35			
28-16	A	20					20			
28-17	A	15					15			
28-18	I	12					12			
28-19	A	10				4	6			
28-20	A	14					10	4		
28-21	A	37					37			
28-22	D	6			3			3		
28-51	D	12					12			
28-59	A	17					7	10		
28-70	A	7				7				
28-72*	I	72								72
28-84	A	9				9				
28-124	A	16				4	12			
28-A29	A	29				2	27			
28-A31*	A	31				6				25
28-A35	A	35						35		
28-A63	I	28					9	19		
28-B1	B	1		1						
28-B2	E	2				2				
32-1	D	5		2			3			
32-2	E	5			3			2		
32-3	D	9		1	2		2	4		
32-5	D	2		2						
32-6	A	23			2	3	2	16		
32-7	I	35					7	28		
32-8	A	30					6	24		
32-9	D	14			2			12		
32-013	D	13					13			
32-13	D	23					5	18		
32-15	D	8		2			6			
32-17	D	4			4					
32-22	A	54						54		
32-31	A	31						31		
32-59	A	42				2		40		
32-68	A	16			4			12		
32-689	A	9			3			6		
32-A5 GM	A	5			5					
32-76	A	19					19			
32-79	D	5			4	1				
32-88	A	54						54		
32-A1	A	1	1							
32-A3	E	3			3					
32-A8	A	8				8				
32-A25	A	25					25			
32-A27	A	27					10	17		
32-A30	A	30					10	20		
32-A40	A	40						40		
32-A48	I	48						48		
32-A55	A	55						55		
32-B22	A	22			2			20		
36-01	C	1	1							
36-3	D	6		3			3			
36-4	A	3		3						
36-5	A	4		4						

Arrangement	Rating	Contact Number	Contact Size							
			4/0	0	4	8	12	16	18	20
36-6	A	6		2	4					
36-7	A	47					7	40		
36-8	A	47					1	46		
36-9	A	31			1	2	14	14		
36-10	A	48						48		
36-14	D	16				5	5	6		
36-15	A	35						35		
36-18 (36-9x100*)	A	31			1	2	14	14		
36-22	D	22					22			
36-35	A	36				4		32		
36-54=36-B39	A	39				8		31		
36-66	A	56					4	52		
36-74	A	44				1		43		
36-77	D	7			7					
36-A7	A	7		3	2		2			
36-A10	A	10			2	8				
36-A35	A	8		4				4		
36-A51	D	6		3	2			1		
36-A72*	I	72					4	16	52	
36-A99*	A	65						15		50
36-B78	D	14				12		2		
36-B90	D	1					n.1 Special Contact			
36-D78	D	14				10		4		
40-1	D	30					6	24		
40-9	A	47				1	22	24		
40-10	A	29			4	9		16		
40-26	A	26				7	19			
40-31	D	31						31		
40-35	D	35						35		
40-47	A	47				1	22	24		
40-53	A	60						60		
40-56	A	85						85		
40-62	A	60						60		
40-63	A	61						61		
40-67	A	11			10			1		
40-100*	A	100							100	
40-150*	I	150							150	
40-951	A	51					25	26		
40-A3	A	5		3			2			
40-A4	A	6		4			2			
40-A5	A	5		3	1		1			
40-A5GM	A	5		5						
40-A6	B	6					6			
40-A8	E	8		4				4		
40-A9	A	9		3		6				
40-A10	D	8			4			4		
40-A14	A	14			8		6			
40-A20	D	20				2	18			
40-A24	D	24				8	16			
40-A38	A	38					38			
40-A51	A	31				15		16		
40-A55	A	5		5						
40-A56	A	85						85		
40-A62	A	62				2	60			
40-A65	A	65						65		
40-A70	A	70						70		
40-B4	E	4		4						
40-B19	A	19				19				
40-B25	A	29		4				25		
40-B37	A	37					37			
40-D4	C	4				4				
40-G4	E	4				4				

\* Only Crimp Contact Version