

MIL-DTL-38999 Series I Type Quick selection guide

QUICK SELECTION GUIDE	
Description	Page
SuperNine Contact, Product Selection Guide	175
D38999 QPL Crimp Contacts and Commercial Crimp Contacts	176
Extended Durability (1500 Cycle) D38999 QPL and Commercial Crimp Contacts	177
Extended Durability D38999 QPL and Commercial Equivalent Crimp Contacts	177
#8 High Power Contacts	177
Size #16 Coaxial Contacts	178
Size #12 Coaxial Contacts	179
Size #12, 75 Ohm Matched Impedance Coaxial Contacts	180
Size #8, 2.5 GHz Max Operating Frequency, 50 Ohm Contacts for Low Loss Coax Cable	182
Size #8, 3 GHz Max Operating Frequency, 50 Ohm Contacts for Coax Cable	184
Size #8, 4 GHz Max Frequency, 75 Ohm Low-Loss, Matched-Impedance Coax Contacts & Cable	186
Size #8 (50Ω and 75Ω) Coaxial Contacts	190
Size #8 Concentric Twinax Contacts	192
Size #8 Quadrax Contacts	199
Thermocouple Contacts	202
Size #12 Pneumatic Contacts	203
Size #8 Cavity Optoelectronic Contact	203
Crimp Contact Termination Instructions	204
Power and Signal Crimp Contact Tool Cross Reference	205
El Ochito® Octaxial "White," "Blue," and "Red" Contacts and Assembly Tools	210
600-280 El Ochito® Contact Termination/Installation Kit	214
Crimp Tools & Positioners	215
Contact Insertion and Extraction Tools	217
Contact Retention Tester for Size #23 Contacts	217
Dummy Contact Sealing Plugs (DCSP)	218
Sealing Plugs	219
Band-Master ATS® Banding Tool	223
600H005 Connector Holding Tool	224



Crimp Contacts



Banding Tool



Contact Retention Tester



Crimp Tool



**Contact Termination/
Installation Kit**