

MIL-DTL-38999 Series I Type Signal and power crimp contact tool cross reference

Signal Crimp Contacts						
Size	Gender	Contact Part Number	Crimp Tool	Positioner	Insertion Tool	Extraction Tool
D38999 QPL and Commercial Contacts						
23	Pin	M39029/122-670	809-015 M22520/2-01	859-210 M22520/2-13	859-163 M81969/1-05	859-163 M81969/1-05
23	Skt	M39029/121-663	809-015 M22520/2-01	859-211 M22520/2-16	859-163 M81969/1-05	859-163 M81969/1-05
22	Pin	850-002-22-360 M39029/58-360	809-015 M22520/2-01	859-018 M22520/2-09	859-163 M81969/14-01	859-163 M81969/14-01
22	Skt	850-001-22-348 M39029/56-348	809-015 M22520/2-01	809-369 M22520/2-07	859-163 M81969/14-01	859-163 M81969/14-01
20	Pin	850-002-20-363 M39029/58-363	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
			809-136 M22520/1-01	809-137 M22520/1-04 (Red)		
20	Skt	800-001-20-351 M39029/56-351	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
			809-136 M22520/1-01	809-137 M22520/1-04 (Red)		
16	Pin	850-002-16-364 M39029/58-364	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03
16	Skt	850-001-16-352 M39029/56-352	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03
12	Pin	850-002-12-365 M39029/58-365	809-136 M22520/1-01	809-137 M22520/1-04 (Yellow)	809-132 M81969/14-04	809-132 M81969/14-04
12	Skt	850-001-12-353 M39029/56-353	809-136 M22520/1-01	809-137 M22520/1-04 (Yellow)	809-132 M81969/14-04	809-132 M81969/14-04
Thermocouple Contacts						
23	Pin	857-104	809-015 M22520/2-01	859-210 M22520/2-13	859-163 M81969/1-05	859-163 M81969/1-05
23	Skt	857-105	809-015 M22520/2-01	859-211 M22520/2-16	859-163 M81969/1-05	859-163 M81969/1-05
22	Pin	850-181-22	809-015 M22520/2-01	859-018 M22520/2-09	859-163 M81969/14-01	859-163 M81969/14-01
22	Skt	850-183-22	809-136 M22520/2-01	809-369 M22520/2-07	859-163 M81969/14-01	809-131 M81969/14-03
20	Pin	850-181-20	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
20	Skt	850-183-20	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
16	Pin	850-181-16	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03
16	Skt	850-183-16	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03

MIL-DTL-38999 Series I Type Signal and power crimp contact tool cross reference

Signal Crimp Contacts						
Size	Gender	Contact Part Number	Crimp Tool	Positioner	Insertion Tool	Extraction Tool
Extended Durability D38999 Contacts						
22	Pin	850-007-22-620 M39029/107-620	809-015 M22520/2-01	859-018 M22520/2-09	859-163 M81969/14-01	859-163 M81969/14-01
22	Skt	850-006-22-614 M39029/106-614	809-015 M22520/2-01	809-369 M22520/2-07	859-163 M81969/14-01	859-163 M81969/14-01
20	Pin	850-007-20-621 M39029/107-621	809-136 M22520/1-01	809-137 M22520/1-04 (Red)	809-207 M81969/14-10	809-207 M81969/14-10
			809-015 M22520/2-01	M22520/2-10		
20	Skt	850-006-20-615 M39029/106-615	809-136 M22520/1-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
			809-015 M22520/2-01	M22520/2-10		
16	Pin	850-007-16-622 M39029/107-622	809-136 M22520/1-01	809-137 M22520/1-04 (blue)	809-131 M81969/14-03	809-131 M81969/14-03
16	Skt	850-006-16-616 M39029/106-616	809-136 M22520/1-01	809-137 M22520/1-04 (blue)	809-131 M81969/14-03	809-131 M81969/14-03
12	Pin	850-007-12-623 M39029/107-623	809-136 M22520/1-01	809-137 M22520/1-04 (yellow)	809-132 M81969/14-04	809-132 M81969/14-04
12	Skt	850-006-12-617 M39029/106-617	809-136 M22520/1-01	809-137 M22520/1-04 (yellow)	809-132 M81969/14-04	809-132 M81969/14-04
SuperNine 233-205 and 233-206 Extended Durability Connector Contacts						
23	Pin	857-189 (AS39029/18 Type)	809-015 M22520/2-01	859-210 M22520/2-13	M81969/16-04	M81969/16-04
23	Skt	857-190 (AS39029/17 Type)	809-015 M22520/2-01	M22520/2-16	M81969/16-04	M81969/16-04
22	Pin	857-151-22 (IAW M39029/58-360)	809-015 M22520/2-01	859-018 M22520/2-09	859-163 M81969/14-01	859-163 M81969/14-01
22	Skt	857-150-22 (IAW M39029/56-348)	809-015 M22520/2-01	809-369 M22520/2-07	859-163 M81969/14-01	859-163 M81969/14-01
20	Pin	857-151-20 (IAW M39029/58-363)	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
			809-136 M22520/1-01	809-137 M22520/1-04 (Red)		
20	Skt	857-150-20 (IAW M39029/56-351)	809-015 M22520/2-01	M22520/2-10	809-207 M81969/14-10	809-207 M81969/14-10
			809-136 M22520/1-01	809-137 M22520/1-04 (Red)		
16	Pin	857-151-16 (IAW M39029/58-364)	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03
16	Skt	857-150-16 (IAW M39029/56-352)	809-136 M22520/1-01	809-137 M22520/1-04 (Blue)	809-131 M81969/14-03	809-131 M81969/14-03
12	Pin	857-151-12 (IAW M39029/58-365)	809-136 M22520/1-01	809-137 M22520/1-04 (Yellow)	809-132 M81969/14-04	809-132 M81969/14-04
12	Skt	857-150-12 (IAW M39029/56-353)	809-136 M22520/1-01	809-137 M22520/1-04 (Yellow)	809-132 M81969/14-04	809-132 M81969/14-04