



MIL-DTL-38999 Series IV Type, QPL Qualified
 38999/41 panel mount receptacle

HERMETIC CONNECTORS



HOW TO ORDER						
Sample Part Number		D38999/41	Y	B	35	P N
D38999	38999/41 = Panel mount receptacle					
Class	N = Hermetic, CRES, nickel finish, conductive, -65°C to 200°C Y = Hermetic, CRES, passivate finish, conductive, -65°C to 200°C H = Hermetic, CRES, passivate finish, conductive, -65°C to 200°C (space grade)					
Shell Size	B, C, D, E, F, G, H, J					
Insert Arrangement	Per MIL-STD-1560; See reference information section for details					
Contact Style	P = Pin, solder cup X = Pin, eyelet C = Pin, PCB flex feedthrough S = Socket, solder cup Z = Socket, eyelet D = Socket, PCB flex feedthrough					
Polarization	N (Normal), A, B, C, D, K, L, M, R ; see polarization positions table					

DIMENSIONS



WIRE ACCOMMODATION	
Contact Size	Wire Gauge
22D	#22 - #28
20	#20 - #24
16	#16 - #20
12	#12 - #14

POLARIZATION POSITION									
	N	A	B	C	D	K	L	M	R
XX	110°	100°	90°	80°	70°	120°	120°	120°	120°
YY	250°	260°	270°	280°	290°	255°	265°	275°	285°