

MIL-DTL-38999 Series III Type Environmental Connectors

Shielded contacts, cable accommodation and assembly tools

HIGH-SPEED CONNECTORS

Shielded Contact Assembly Tools								
Contact PN	Size	Cable Accomodated	Max Freq. (MHz)	Inner Contact		Cable Shield Hex		Insertion/ Removal Tool
				Tool	Positioner	Tool	Hex Die	
852-008 M39029/76	16	RG174, RG316, RG178, RG179	500	809-015	809-125	809-127	809-126	809-131
852-009 M39029/77	16	RG174, RG316, RG178, RG179	500	809-015	809-125	809-127	809-126	
852-004 M39029/102	12	RG174, RG179, RG180, RG316	3K	809-128	859-006	809-129	809-130	809-132
852-005 M39029/103	12	RG174, RG179, RG180, RG316	3K	809-128	859-006	809-129	809-130	809-132
852-007 M39029/60-637	8	RG180	700	809-015	859-050	809-129	859-051	859-022
852-006 M39029/59-366	8	RG180	700	809-015	859-050	809-129	859-051	859-022
852-056-01 75 ohm	8	V75268, V76261, V73263	4K	809-015	809-240	809-129	859-047	859-049
852-056-02 75 ohm	8	RG179	4K	809-015	809-240	809-129	809-130	859-049
852-057-01 75 ohm	8	V75268, V76261, V73263	4K	809-015	809-240	809-129	859-047	859-049
852-057-02 75 ohm	8	RG179	4K	809-015	809-240	809-129	809-130	859-049
853-014	8	M17/176-00002	20	809-015	809-240	809-129	859-007	859-049
853-013	8	M17/176-00002	20	809-015	809-240	809-129	859-007	859-049
854-001	8	Tensolite NF26Q100	3K	809-015	809-240	809-129	859-007	859-049
	8	Tensolite NF24Q100, PIC E51424	3K	809-015	809-240	809-129	859-007	859-049
	8	Draka Fileca F 4704-6	3K	809-015	809-240	809-129	859-007	859-049
	8	Draka Fileca F 4704-4	3K	809-015	809-240	809-129	859-007	859-049
	8	Tensolite NF22Q100	3K	809-015	809-240	809-129	859-007	859-049
854-002	8	Tensolite NF26Q100	3K	809-015	809-240	809-129	859-007	859-049
	8	Tensolite NF24Q100, PIC E51424	3K	809-015	809-240	809-129	859-007	859-049
	8	Draka Fileca F 4704-6	3K	809-015	809-240	809-129	859-007	859-049
	8	Draka Fileca F 4704-4	3K	809-015	809-240	809-129	859-007	859-049
	8	Tensolite NF22Q100	3K	809-015	809-240	809-129	859-007	859-049
853-003 M39029/113-625	8	M17/176-00002	10K	809-015	809-240	809-129	859-048	859-048
853-004 M39029/114-628	8	M17/176-00002	10K	809-015	809-240	809-129	859-048	859-048

Please refer to section J for power and signal contact assembly tools