



**SUPERSEAL™**

## Ruggedized RJ45 and USB connectors for applications as diverse as military ground vehicles to passenger IFE

IP67 open-face, robust insert-to-shell grounding, complete range of wire, cable, and circuit board terminations

- Superior sealing—IP67 unmounted—for complete system protection against water, sand and dust
- Highly durable RJ45 design, including enhanced operating temperature, increased life-cycle, and rugged vibration and shock performance
- Shielded/grounded coupler designs in both receptacle and plug connectors
- Crimp, solder-cup, PC tail, and Quadrax contact/wire termination options
- RJ45 plug and/or jack interface options available in Cat 5e
- MIL-DTL-38999 type versions intermateable with other RJ45 field-duty connectors



MIL-DTL-38999 Series III  
with sealed RJ45



MIL-DTL-38999 Series III  
with RJ45 USB cable assemblies



High-capacity, high-speed  
USB data stick



RJ45 ETHERNET AND USB 2.0  
**Introduction and Technical Reference**  
 SuperSeal connector overview



**A**

**AVAILABLE TERMINATION OPTIONS**



**EXPANDED PACKAGING OPTIONS**



**ACCESSORIES AND TOOLS**

