



RJ12, RJ45, AND USB 2.0 TYPE A SuperSeal™ 28840 Type Connectors

Product Selection Guide



H



900-320

Page H-2

SuperSeal™ Coupler with Accessory Threads and RJ12 Plug-to-Jack (Plug) or Jack-to-Jack (Receptacle).



900-300

Page H-4

SuperSeal™ Coupler with Accessory Threads and RJ45 Plug-to-Jack (Plug) or Jack-to-Jack (Receptacle).



900-301

Page H-6

SuperSeal™ Connector with Accessory Threads and RJ45 Plug (Plug) or Jack (Receptacle) to Crimp Removable Contacts.



900-340

Page H-8

SuperSeal™ Coupler with Accessory Threads and USB Male-to-Female (Plug) or Female-to-Female (Receptacle).



900-345

Page H-10

SuperSeal™ Connector with Accessory Threads and USB Male (Plug) or Female (Receptacle) to Crimp Removable Contacts.