

ULTRA HIGH-TEMPERATURE TOLERANT ThermaRex UHT Interconnect Ecosystem

ThermaRex™
CRYO • HIGH TEMP • ULTRA HIGH-TEMP

SuperNine® Better-than-QPL D38999 Series III Packaging 2570-2248

2570-2248 CONNECTOR, JAM NUT MOUNT, THERMAREX UHT, 600°C, RECEPTACLE



How To Order		-24	Z1	13E	-4	P	N
Sample Part Number	2570-2248						
Series / Basic Part No.	2570-2249 Connector, Jam Nut Mount, ThermaRex UHT, Receptacle						
Connector Style	24 = Receptacle, Jam Nut						
Material/Finish	Z1 = Passivated stainless steel						
Shell Size	13E						
Insert Arrangement	4						
Contact Style	P = Pin Contact						
Alternate Polarization	A, B, C, D, E, N = Normal, U = Universal						

THERMAREX™ UHT

NOTES

- This connector is temperature rated from -65°C to +600°C.
- This connector is designed to mate with 2570-2248 with the same arrangement, polarization, and opposite contact gender.

MATERIAL/FINISH

- Barrel, Coupling Nut - Inconel / Nickel Plate
- Insulator - High Grade Ceramic / N.a.
- Socket Contact - Inconel / Nickel Plate

