


El Ochito® Connector Selection Guide

El Ochito® Connector Selection Guide

Series 801 Mighty Mouse




- High performance ultraminiature circular
- Double-start mating threads
- Compatible with MIL-DTL-38999 type size 8 El Ochito® contacts
- 10 arrangements, up to 5 El Ochito® contacts per connector

For More Information

Plugs, Band Platform..... 801-007⁽¹⁾
 Plugs, Accessory Thread..... 801-008⁽¹⁾
 Receptacles, Band Platform..... 801-009⁽¹⁾
 Receptacles, Accessory Threads..... 801-010⁽¹⁾
 Receptacles, Straight PC Tail..... 801-120⁽²⁾
 (1) Series 80 Mighty Mouse Catalog
 (2) Contact Glenair for data sheet.

Series 805 Mighty Mouse



- High performance ultraminiature circular
- Triple-start ACME mating threads
- Compatible with MIL-DTL-38999 type size 8 El Ochito® contacts
- 10 arrangements, up to 5 El Ochito® contacts per connector

For More Information

Plugs, Band Platform..... 805-001⁽¹⁾
 Plugs, Accessory Thread..... 805-002⁽¹⁾
 Receptacles, Band Platform..... 805-003⁽¹⁾
 Receptacles, Accessory Threads..... 805-004⁽¹⁾
 Receptacles, Straight PC Tail..... 805-126⁽²⁾
 (1) Series 80 Mighty Mouse Catalog
 (2) Contact Glenair for data sheet

Series 233 SuperNine®



- MIL-DTL-38999 Series III
- Triple-start ACME mating threads
- High vibration, high temperature
- 20 contact arrangements
- Contact alignment keyway
- Compatible with M85049 accessories

For More Information

Plugs, Receptacles..... 233-231 & 233-232⁽¹⁾
 Receptacles, Straight PC Tail..... 233-229⁽¹⁾
 (1) SuperNine Catalog

For environmental backshell, see part number 377HS121

Series 882 SuperFly®



- Ultra-small, lightweight
- Push-pull or threaded coupling
- High shock and vibration
- Robust EMI shielding
- IP67 immersion rating

For More Information


Push-Pull Plug..... 882-001⁽¹⁾
 Push-Pull Receptacle..... 882-002⁽¹⁾
 Push-Pull Receptacle, PC Tail..... 882-005⁽¹⁾
 Plug, Threaded Coupling..... 882-003⁽¹⁾
 Receptacle, Threaded Coupling..... 882-006⁽¹⁾
 Recep, Threaded, PC Tail 882-004⁽¹⁾
 (1) Contact Glenair for data sheet

For details see our Series 882 SuperFly catalog

El Ochito[®] Connector Selection Guide

El Ochito[®] Connector Selection Guide

Series 792 Ultraminiature Rectangular



- Next-generation rear release rectangular
- 1 – 9 El Ochito[®] contacts
- Dual lobe shell polarization
- Scoop-proof interface
- Straight and right angle PC tail
- Environmentally sealed
- EMI protected
- Guide Pins for blind mate

For More Information

Plugs, Free-Hanging	792-001 ⁽¹⁾
Receptacles, Free-Hanging	792-002 ⁽¹⁾
Plugs, Panel Mount	792-003 ⁽¹⁾
Receptacles, Panel Mount	792-004 ⁽¹⁾
Plugs, Straight PC Tails	792-005 ⁽¹⁾
Receptacles, Straight PC Tails	792-006 ⁽¹⁾
Plug, Straight PC Tails, Panel Mt.	792-007 ⁽¹⁾
Recep, Straight PC Tails, Panel Mt.	792-008 ⁽¹⁾
Plugs, 90° PC Tails	792-009 ⁽¹⁾
Receptacles, 90° PC Tails	792-010 ⁽¹⁾
Plugs, 90° PC Tails, Panel Mt.	792-011 ⁽¹⁾
Recep, 90° PC Tails, Panel Mt	792-012 ⁽¹⁾

(1) Contact Glenair for data sheet.

Series 28 HiPer-D[®]



- Standard M24308 interface dimensions
- Rugged machined 6061 aluminum shell
- Grounded metal insert
- 2 – 5 El Ochito[®] contacts
- Straight PC tail
- EMI protected

For More Information

Plugs, Free-Hanging	280-082 ⁽¹⁾
Receptacles, Free-Hanging	280-083 ⁽¹⁾
Plugs, Straight PC Tails	280-090 ⁽²⁾
Receptacles, Straight PC Tails	280-091 ⁽²⁾

(1) Series 28 HiPer-D Catalog

(2) Contact Glenair for data sheet