


## Ordering Information: El Ochito® White Contacts

El Ochito® Contacts: How To Order									
Data Protocol	Connector Type	Wire Size	Cable Type	Cable		El Ochito® Type I		El Ochito® Type II	
				Glenair Part No. <i>(Mfg. P/N)</i>	Cable Dia.	Pin Contact <i>Assembly Instr.</i>	Skt Contact <i>Assembly Instr.</i>	Pin Contact <i>Assembly Instr.</i>	Skt Contact <i>Assembly Instr.</i>
1000BASE-T 10GBASE-T  El Ochito® White	ARINC 600	26	S/UTP	963-003-26 <i>(PIC E6A3826)</i>	.220 (5.56)	858-009-01 AI85074-01	858-010-01 AI85074-01		
			S/FTP	963-033-26 <i>(Gore RCN9047-26)</i>	.220 (5.56)	858-009-02 AI85084-01	858-010-02 AI85084-01		
	Series 23 SuperNine® Series 80 Mighty Mouse Series 28 HiPer-D®	24	S/UTP	963-037-24 <i>(PIC E6A3824)</i>	.260 (6.60)			858-005-03 AI85097-03	858-006-03 AI85097-03
			S/FTP	963-033-24 <i>(Gore RCN9047-24)</i>	.260 (6.60)			858-005-04 AI85097-04	858-006-04 AI85097-04
		26	S/UTP	963-003-26 <i>(PIC E6A3826)</i>	.220 (5.56)	858-003-01F AI85048-01	858-004-01F AI85048-01	858-005-01 AI85097-01	858-006-01 AI85097-01
			S/FTP	963-033-26 <i>(Gore RCN9047-26)</i>	.220 (5.56)	858-003-02F AI85048-02	858-004-02F AI85048-02	858-005-02 AI85097-01	858-006-02 AI85097-01
	Series 79	26	S/UTP	963-003-26 <i>(PIC E6A3826)</i>	.220 (5.56)	858-003-01F AI85048-01	858-032-01F AI85112-01		
			S/FTP	963-033-26 <i>(Gore RCN9047-26)</i>	.220 (5.56)	858-003-02F AI85048-02	858-032-02F AI85112-02		
	EPXB	26	S/UTP	963-003-26 <i>(PIC E6A3826)</i>	.220 (5.56)	858-014-02F AI85099-01	858-015-02F AI85099-01		
			S/FTP	963-033-26 <i>(Gore RCN9047-26)</i>	.220 (5.56)	858-014-01F AI85105-01	858-015-01F AI85105-01		

## Ordering Information: El Ochito® Blue and Red Contacts

El Ochito® Contacts: How To Order								
Data Protocol	Connector Type	Wire Size	Cable Type	Cable		El Ochito® Type I		
				Glenair Part No. <i>(Mfg. P/N)</i>	Cable Dia.	Pin Contact <i>Assembly Instr.</i>	Socket Contact <i>Assembly Instr.</i>	
SuperSpeed USB  El Ochito® Blue	ARINC 600	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	<b>858-038-01</b> <i>AI852124-01</i>	<b>858-035-01</b> <i>AI852124-01</i>	
			Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	<b>858-038-02</b> <i>AI85124-02</i>	<b>858-035-02</b> <i>AI85124-02</i>	
	Series 79	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	<b>858-028-01F</b> <i>AI85114-02</i>	<b>858-040-01F</b> <i>AI85125-01</i>	
			Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	<b>858-028-02F</b> <i>AI85090-01</i>	<b>858-040-02F</b> <i>AI85125-02</i>	
	Series 23 SuperNine® Series 80 Mighty Mouse Series 28 HiPer-D®	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	<b>858-028-01F</b> <i>AI85114-02</i>	<b>858-029-01F</b> <i>AI85114-02</i>	
			Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	<b>858-028-02F</b> <i>AI85090-01</i>	<b>858-029-02F</b> <i>AI85090-01</i>	
	HDMI, DisplayPort, SATA  El Ochito® Red	ARINC 600	26	Cat 6a S/FTP	963-033-26 <i>(Gore RCN9047-26)</i>	.220 (5.56)	<b>858-039-01</b> <i>AI85084-01</i>	<b>858-037-01</b> <i>AI85084-01</i>
		Series 79	26				<b>858-030-02F</b> <i>AI85048-02</i>	<b>858-041-01F</b> <i>AI85112-02</i>
Series 23 SuperNine® Series 80 Mighty Mouse Series 28 HiPer-D®		26	<b>858-030-02F</b> <i>AI85048-02</i>				<b>858-031-02F</b> <i>AI85048-02</i>	