



**SERIES 77 SHRINK BOOTS**  
**Heat Shrink Boots**  
**Boot Selection Guide**



**A**

**Lipped Shrink Boots for Use with Boot Adapters:**



**Standard Boots**

770-001S, 770-003S, 770-016S,  
 770-001A, 770-003A, 770-033A,  
 770-001B, 770-003B and 770-034  
 Available in twelve sizes in straight, 90°, 45°, and 30° profiles. Standard boots fit adapters from .250" (6.35) to 2.470" (62.70) diameter.



**Short Boots**

770-002S, 770-004S, 770-017S  
 Available in seven sizes, short boots fit adapters from .450" (11.43) to 2.470" (62.70) diameter. Use where space is limited.



**Long Tail Boots**

770-006S, 770-020S, 770-006A, 770-021A  
 Available in eleven sizes (straight) and nine sizes (right angle). Long tail boots fit adapters from .500" (12.70) to 3.200" (81.30) diameter, providing added protection to open wire bundles or extra-long stripped cable ends.



**High Ratio Boots**

770-007S, 770-007A  
 Available in four sizes, in straight and 90° profiles. High ratio boots fit adapters from .525" (13.34) to 1.650" (41.91) diameter. Use high ratio boots when wire bundle or cable diameter is smaller than normal.



**Heavy Wall**

770-018S, 770-008S  
 Available in six sizes and fit adapters from .350" (8.89) to 2.550" (64.80) diameter. 770-008S available in 2010 material only 770-018 available in any material



**Convuluted Boots**

770-022C  
 Available in seven sizes, convoluted boots fit adapters from .250" (6.35) to 1.500" (38.10)

**Lipless Boots for Direct Connector Attachment:**



**Standard Boots**

770-005S, 770-019SB, 770-005A  
 Available in eleven sizes (straight) and eight sizes (right angle). Standard straight boots fit connectors from .250" (6.35) to 3.200" (81.30) diameter. Right angle boots fit connectors from .250" (6.35) to 2.000" (50.80) diameter.

**Connector Specific Boots for Glenair Connectors:**



**Series Specific**

770-028S 38999 SuperSeal®  
 770-029S Nanominiature  
 770-030 HiPer-D® Elliptical  
 770-031S SuperFly® Straight  
 770-031A SuperFly® 90  
 809-060 Mighty Mouse

Available for various Glenair connector families. These boots are developed specifically for our ever growing Interconnect product lines and backshell accessories.

**Multi-Leg "Wye" and "Tee" Boots for Cable Assembly Routing Transitions:**



**"Wye" Transitions**

770-009Y, 770-010Y  
 Available in seven sizes and two body styles (low profile and wide body), "Y" transitions fit cables from Ø .200" (5.08) to .400" (10.16)



**"Tee" Transitions**

770-011T, 770-012T  
 Available in four sizes and two body styles (low profile and wide body), "T" transitions fit cables from Ø .100" (2.54) to 1.250" (31.75)



**1:3 and 1:4 Transitions**

770-013, 770-014, 770-015  
 Available in 1 to 3 (low profile and wide body) and 1 to 4 (wide body), multi-leg transitions fit cables from Ø .200" (5.08) to 2.00" (50.8)