

SERIES 680 Grounding Plates




680-162 Grounding Plate



HOW TO ORDER			
Sample Part Number	680-162	-16	A
Basic Part Number	680-162 Grounding Plate		
Dash Number	See Table I		
Style	A, B, C		

TABLE I - DIMENSIONS



Dash No	Type	A Sqr	AA Sqr	B Sqr	C Dia	D Dia	E	F	G	H Dia	Length
7	I	0.469 (11.91)	-	0.740 (18.80)	0.443 (11.25)	0.125 (3.18)	0.201 (5.11)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
8	I	0.531 (13.49)	-	0.812 (20.62)	0.505 (12.83)	0.125 (3.18)	0.263 (6.68)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
9	I	0.594 (15.09)	-	0.875 (22.23)	0.572 (14.53)	0.125 (3.18)	0.326 (8.28)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
10	I	0.625 (15.88)	-	0.903 (22.94)	0.640 (16.26)	0.125 (3.18)	0.357 (9.07)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
11	II	0.719 (18.26)	0.670 (17.02)	1.019 (25.88)	0.719 (18.26)	0.125 (3.18)	0.433 (11.00)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
12	II	0.812 (20.62)	0.765 (19.43)	1.104 (28.04)	0.855 (21.72)	0.125 (3.18)	0.530 (13.46)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
14	II	0.906 (23.01)	0.859 (21.82)	1.198 (30.43)	0.984 (24.99)	0.125 (3.18)	0.624 (15.85)	0.50 (12.70)	0.500 (12.70)	0.147 (3.73)	3.00 (76.20)
16	II	0.969 (24.61)	0.938 (23.83)	1.281 (32.54)	1.094 (27.79)	0.125 (3.18)	0.687 (17.45)	0.70 (17.78)	0.750 (19.05)	0.173 (4.39)	4.00 (101.60)
18	II	1.062 (26.97)	1.016 (25.81)	1.395 (35.43)	1.220 (30.99)	0.125 (3.18)	0.780 (19.81)	0.70 (17.78)	0.750 (19.05)	0.173 (4.39)	4.00 (101.60)
20	II	1.187 (30.15)	1.109 (28.17)	1.515 (38.48)	1.345 (34.16)	0.156 (3.96)	0.874 (22.20)	0.70 (17.78)	0.750 (19.05)	0.173 (4.39)	4.00 (101.60)
22	II	1.250 (31.75)	1.203 (30.56)	1.645 (41.78)	1.478 (37.54)	0.156 (3.96)	0.968 (24.59)	1.00 (25.40)	1.000 (25.40)	0.268 (6.81)	5.00 (127.00)
24	II	1.375 (34.93)	1.312 (33.32)	1.770 (44.96)	1.595 (40.51)	0.156 (3.96)	1.031 (26.19)	1.00 (25.40)	1.000 (25.40)	0.268 (6.81)	5.00 (127.00)
25	I	1.500 (38.10)	1.437 (36.50)	1.861 (47.27)	1.658 (42.11)	0.156 (3.96)	1.125 (28.58)	1.00 (25.40)	1.000 (25.40)	0.268 (6.81)	5.00 (127.00)

680-162 Grounding Plate



TABLE II												
Dash No	MIL-DTL-38999				MIL-DTL -5015	Series 806	AS81703 Series 3	MIL-DTL-26482 Series 1&2	MIL-DTL-83723 Series III	MIL-DTL-26500 NAS 1599	MIL-C -81511	MIL-DTL -27599
	Series I	Series II	Series III	Series IV								
7	-	-	-	-	-	7	-	-	-	-	-	-
8	-	-	-	-	-	8	-	-	-	-	-	-
9	-	8	-	-	8S	9	-	8	8	8	8	8
10	-	-	-	-	-	10	3	-	-	-	-	-
11	9	10	9(A)	-	10SL	11	-	10	10	10	10	10
12	11	12	11(B)	11(B)	12,12S	12	12	12	12	12	-	12
14	13	14	13(C)	13(C)	14,14S	14	19	14	14	14	14	-
16	15	16	15(D)	15(D)	16,16S	16	27	16	16	16	16	14
18	17	18	17(E)	17(E)	18	18	-	18	18	18	18	16
20	19	20	19(F)	19(F)	20	20	37	20	20	20	20	-
22	21	22	21(G)	21(G)	22	22	-	22	22	22	22	-
24	23	24	23(H)	23(H)	24	24	-	24	24	24	24	-
25	25	-	25(J)	25(J)	-	-	51	-	-	-	-	-