

MIL-DTL-26482 Type Quick Release Bayonet Hermetic Connectors



MIL-DTL-26482
Type

A Comprehensive Line of MIL-DTL-26482 Series I and II Type Bayonet Glass Sealed Hermetic Connectors

MIL-DTL-26482 Series I and II Bayonet Lock Connectors are general purpose medium density connectors, with a variety of mounting styles including bulkhead feed-thrus, jam-nut, flange mount and solder cup receptacles. All feature quick release

bayonet coupling. 9 shell sizes with up to 61 AWG contacts in size #20, #16, and #12 and #8 are offered. Material and finish options include titanium and Inconel®, and space grade screening is available.

D

Quick Selection Guide		
Part Number	Description	Page
	MIL-DTL-26482 Type Insert Arrangements	D-2
	MIL-DTL-26482 Type Alternate Key Positions	D-3
	Glenair Hermetic Connector Products Special Leak Rate Mod Codes	D-4
	Glenair Hermetic Connector Products Space Grade Mod Codes	D-5
230-014	Bayonet Coupling Solder Mount Receptacle MS3113 Type	D-6
230-015	Bayonet Coupling Jam Nut Receptacle MS3114 Type	D-8
947-303	Narrow Flange Mount Bulkhead Feed-Thru MS3440 Type	D-10
230-035	Bayonet Coupling Narrow Flange Mount Receptacle MS3112 Type	D-12
230-016	Bayonet Coupling Narrow Flange Mount Receptacle MS3440 Type	D-14
230-017	Bayonet Coupling Wide Flange Mount Receptacle MS3442 Type	D-16
230-018	Bayonet Coupling Solder Flange Mount Receptacle MS3443 Type	D-18
230-019	Quick Release Bayonet Receptacle, Single Hole Jam Nut MS3449 Type	D-20
230-020	Bayonet Coupling Solder Mount Receptacle with Solderless Contacts MS3473 Type	D-22
230-021	Bayonet Coupling Box Mount Receptacle with Solderless Contacts MS3477 Type	D-24
230-022	Bayonet Coupling Jam Nut Mount Receptacle with Solderless Contacts MS3479 Type	D-26
237-034	Bayonet Coupling Jam Nut Receptacle MS3449 Type	D-28
230-051	Special Narrow Square Flange Mount Hermetic Receptacle MS3440 Type	D-30
230-133	Square Flange Mount Hermetic Receptacle MS3112 Type	D-32
237-240	MIL-DTL-26482 Series I Connector, Special Square Flange Mount, Bayonet Coupling	D-34
257-135	Bayonet Coupling Jam Nut Mount Pin/Pin Bulkhead Feed-Thru Receptacle	D-36
947-292	Bayonet Coupling Jam Nut Mount Bulkhead Feed-Thru Receptacle	D-38

Dimensions in Inches (millimeters) are subject to change without notice.

© 2013 Glenair, Inc.

Rev 11/17/17

U.S. CAGE Code 06324

Printed in U.S.A.