


SERIES 80

Mighty Mouse Connectors and Cables



Jam-Nut, Rear Panel Mount, Cutout Dimensions  
Series 803, 804, and 805

**SERIES 803, 804, 805 REAR PANEL MOUNT JAM-NUT PANEL, CUTOUT DIMENSIONS**



Rear Panel Mount Connectors

803 Series			804 Series			805 Series		
Shell Size	A Flat	ØB	Shell Size	A Flat	ØB	Shell Size	A Flat	ØB
5	.357 (9.07)	.385 (9.78)	5	.425 (10.80)	.448 (11.38)	8	.545 (13.84)	.572 (14.53)
	.353 (8.97)	.380 (9.65)		.421 (10.69)	.443 (11.25)		.541 (13.74)	.567 (14.40)
6	.417 (10.59)	.447 (11.35)	6	.480 (12.19)	.510 (12.95)	9	.671 (17.04)	.698 (17.73)
	.413 (10.49)	.442 (11.23)		.476 (12.09)	.505 (12.83)		.667 (16.94)	.693 (17.60)
7	.543 (13.79)	.577 (14.66)	7	.604 (15.34)	.635 (16.13)	10	.671 (17.04)	.698 (17.73)
	.539 (13.69)	.567 (14.40)		.600 (15.24)	.630 (16.00)		.667 (16.94)	.693 (17.60)
8	.603 (15.32)	.635 (16.13)	8	.604 (15.34)	.635 (16.13)	11	.731 (18.57)	.760 (19.30)
	.599 (15.21)	.630 (16.00)		.600 (15.24)	.630 (16.00)		.727 (18.47)	.755 (19.18)
9	.603 (15.32)	.635 (16.13)	9	.665 (16.89)	.698 (17.73)	12	.794 (20.17)	.822 (20.88)
	.599 (15.21)	.630 (16.00)		.661 (16.79)	.693 (17.60)		.790 (20.07)	.817 (20.75)
10	.731 (18.57)	.760 (19.30)	10	.731 (18.57)	.760 (19.30)	13	.853 (21.67)	.885 (22.48)
	.727 (18.47)	.755 (19.18)		.7427 (18.86)	.755 (19.18)		.849 (21.56)	.880 (22.35)
12	.852 (21.64)	.885 (22.48)	12	.853 (21.67)	.885 (22.48)	15	.980 (24.89)	1.3010 (33.05)
	.848 (21.54)	.880 (22.35)		.849 (21.56)	.880 (22.35)		.976 (24.79)	1.005 (25.53)
14	1.032 (26.21)	1.072 (27.23)	14	.978 (24.84)	1.010 (25.65)	18	1.157 (29.39)	1.198 (30.43)
	1.028 (26.11)	1.067 (27.10)		.974 (24.74)	1.005 (25.53)		1.153 (29.29)	1.193 (30.30)
15	1.103 (28.02)	1.135 (28.83)				19	1.231 (31.27)	1.260 (32.00)
	1.099 (27.91)	1.130 (28.70)					1.227 (31.17)	1.255 (31.88)
						21	1.360 (34.54)	1.385 (35.18)
							1.356 (34.44)	1.380 (35.05)
						23	1.480 (37.59)	1.510 (38.35)
							1.476 (37.49)	1.505 (38.23)