





SERIES 800 UN THREAD MATING
Mighty Mouse Connectors and Cables
 Contact Arrangements,
 Mating Face of Pin Insert Shown



SIZE #23 CONTACTS, TESTED AT 750 VAC




Insert Arrangement	5-3	6-4	6-6	6-7	7-10	8-13
No. of Contacts	3	4	6	7	10	13




Insert Arrangement	9-19	10-26	12-37
No. of Contacts	19	26	37

SIZE #20HD CONTACTS, TESTED AT 1000 VAC




Insert Arrangement	6-23	7-25	8-28	9-210	12-220
No. of Contacts	3	5	8	10	20

SIZE #16 CONTACTS, TESTED AT 1800 VAC




Insert Arrangement	6-1	8-2	9-4	10-5	12-7
No. of Contacts	1	2	4	5	7

SIZE #12 CONTACTS, TESTED AT 1800 VAC



Insert Arrangement	7-1	10-2	12-2	12-3
No. of Contacts	1	2	2	3

SERIES 800 UN THREAD MATING




SERIES 800 UN THREAD MATING
Mighty Mouse Connectors and Cables



Contact Arrangements,
Mating Face of Pin Insert Shown

SIZE #20 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC




Insert Arrangement	8-200		9-201	
Contact Size	#20	#23	#20	#23
No. of Contacts	2	4	2	8

SIZE #16 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC




Insert Arrangement	9-200		10-202	
Contact Size	#16	#23	#16	#23
No. of Contacts	2	4	2	8

SIZE #12 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC



Insert Arrangement	10-200		10-201		12-200		12-201	
Contact Size	#12	#23	#12	#23	#12	#23	#12	#23
No. of Contacts	1	12	2	4	2	6	2	10


SERIES 800 UN THREAD MATING



SERIES 800 UN THREAD MATING
Mighty Mouse Connectors and Cables
 Contact Arrangements,
 Mating Face of Pin Insert Shown




SIZE #16 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 1300 VAC



Insert Arrangement	12-202		12-203	
Contact Size	#16	#23	#16	#23
No. of Contacts	2	20	4	12

SIZE #12 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 1300 VAC



Insert Arrangement	12-204		12-205	
Contact Size	#12	#23	#12	#23
No. of Contacts	2	12	4	4

SERIES 800 UN THREAD MATING