


SERIES 801 DOUBLE-START ACME THREAD Mighty Mouse Connectors and Cables




Contact Arrangements, Mating Face of Pin Insert Shown


SIZE #23 CONTACTS, TESTED AT 750 VAC



Insert Arrangement	5-3	6-4	6-6	6-7	7-10	8-13
No. of Contacts	3	4	6	7	10	13




Insert Arrangement	9-19	10-26	11-31	13-37	16-55
No. of Contacts	19	26	31	37	55




Insert Arrangement	17-85	19-100	21-130
No. of Contacts	85	100	130


SIZE #20HD CONTACT ARRANGEMENTS, TESTED AT 1000 VAC



Insert Arrangement	6-23	7-25	8-28	9-210	13-220
No. of Contacts	3	5	8	10	20



Insert Arrangement	16-235	17-241	19-255	21-269
No. of Contacts	35	41	55	69




SERIES 801 DOUBLE-START ACME THREAD Mighty Mouse Connectors and Cables




Contact Arrangements, Mating Face of Pin Insert Shown

SIZE #16 CONTACT ARRANGEMENTS, TESTED AT 1800 VAC




Insert Arrangement	6-1	8-2	9-4	10-5	13-7
No. of Contacts	1	2	4	5	7




Insert Arrangement	16-12	17-14	19-19	21-22
No. of Contacts	12	14	19	22

SIZE #12 CONTACT ARRANGEMENTS, TESTED AT 1800 VAC



Insert Arrangement	7-1	10-2	13-2	13-3
No. of Contacts	1	2	2	3



Insert Arrangement	16-4	16-5	17-7	21-12
No. of Contacts	4	5	7	12




SERIES 801 DOUBLE-START ACME THREAD Mighty Mouse Connectors and Cables




Contact Arrangements, Mating Face of Pin Insert Shown

SIZE #8 CONTACT ARRANGEMENTS, TESTED AT 1800 VAC




Insert Arrangement	8-1	16-2	17-3	19-4	21-5
Metal Insert Arrangement	8G1	16G2	17G3	19G4	21G5
No. of Contacts	1	2	3	4	5

SIZE #20 AND SIZE #23 SIGNAL, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC




Insert Arrangement	8-200		9-201	
Contact Size	#20	#23	#20	#23
No. of Contacts	2	4	2	8

SIZE #16 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC




Insert Arrangement	9-200		10-202		17-206	
Contact Size	#16	#23	#16	#23	#16	#23
No. of Contacts	2	4	2	8	4	58

SIZE #12 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 750 VAC



Insert Arrangement	10-200		10-201		13-200		13-201	
Contact Size	#12	#23	#12	#23	#12	#23	#12	#23
No. of Contacts	1	12	2	4	2	6	2	10




SERIES 801 DOUBLE-START ACME THREAD Mighty Mouse Connectors and Cables




Contact Arrangements, Mating Face of Pin Insert Shown

SIZE #16 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 1300 VAC




Insert Arrangement	13-202		13-203		16-204		16-205		17-203	
Contact Size	#16	#23	#16	#23	#16	#23	#16	#23	#16	#23
No. of Contacts	2	20	4	12	2	40	4	32	4	40

SIZE #12 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 1300 VAC



Insert Arrangement	13-204		13-205		16-206		16-207		17-204	
Contact Size	#12	#23	#12	#23	#12	#23	#12	#23	#12	#23
No. of Contacts	2	12	4	4	2	34	4	20	4	28

SIZE #8 AND SIZE #23, COMBO CONTACT ARRANGEMENTS, TESTED AT 1300 VAC



Insert Arrangement	11-201		16-208		17-205		19-201		19-202		21-200	
Contact Size	#8	#23	#8	#23	#8	#23	#8	#23	#8	#23	#8	#23
No. of Contacts	1	18	1	32	1	40	2	44	4	12	4	28