

SERIES 89 NANOMINIATURE Rectangular and Circular Connectors



Anti-Static Thermoplastic Dust Covers

Anti-Static Dust Caps



Anti-Static Dust Caps offer protection to Nano connectors for storage and handling. Molded in black thermoplastic LDPE, these caps meet the anti-static decay rate specified in MIL-PRF-81705D. **UL 94-V0** rated, self-extinguishing.

INTRODUCTION



DUST COVER DIMENSIONS

890 Single Row	Contacts	A Ref.
Part Number	Layout	In.
000-01-05-174	5P	.215 (5.46)
000-01-09-174	9P	.315 (8.00)
000-01-15-174	15P	.465 (11.81)
000-01-21-174	21P	.615 (15.62)
000-01-25-174	25P	.715 (18.16)
000-01-31-174	31P	.865 (21.97)
000-01-37-174	37P	1.015 (25.78)
000-01-51-174	51P	1.365 (34.67)
000-01-05-175	5S	.431 (10.95)
000-01-09-175	9S	.531 (13.49)
000-01-15-175	15S	.681 (17.30)
000-01-21-175	21S	.831 (21.11)
000-01-25-175	25S	.931 (23.65)
000-01-31-175	31S	1.081 (27.46)
000-01-37-175	37S	1.231 (31.27)
000-01-51-175	51S	1.581 (40.16)
891 Dual Row	Contacts	A Ref.
000-01-09-176	9P	.191 (4.85)
000-01-15-176	15P	.266 (6.76)
000-01-21-176	21P	.341 (8.66)
000-01-25-176	25P	.391 (9.93)
000-01-31-176	31P	.466 (11.84)
000-01-37-176	37P	.541 (13.74)
000-01-41-176	41P	.591 (15.01)
000-01-51-176	51P	.716 (18.19)
000-01-65-176	65P	.891 (22.63)
000-01-69-176	69P	.941 (23.90)
000-01-85-176	85P	1.141 (28.98)
000-01-91-176	91P	1.216 (30.89)
000-01-09-177	9S	.406 (10.31)
000-01-15-177	15S	.481 (12.22)
000-01-21-177	21S	.556 (14.12)
000-01-25-177	25S	.606 (15.39)
000-01-31-177	31S	.681 (17.30)
000-01-37-177	37S	.756 (19.20)
000-01-41-177	41S	.806 (20.47)
000-01-51-177	51S	.931 (23.65)
000-01-65-177	65S	1.106 (28.09)
000-01-69-177	69S	1.156 (29.36)
000-01-85-177	85S	1.408 (35.76)
000-01-91-177	91S	1.483 (37.67)



000-01-00-174 Single Row Plug





000-01-00-175 Single Row Receptacle



000-01-00-176 Dual Row Plug



000-01-00-177 Dual Row Receptacle



SERIES 89 NANOMINIATURE Rectangular and Circular Connectors



Anti-Static Thermoplastic Dust Covers


INTRODUCTION

Anti-Static Dust Caps

Anti-Static Dust Caps offer protection to Nano connectors for storage and handling. Molded in black thermoplastic LDPE, these caps meet the anti-static decay rate specified in MIL-PRF-81705D. **UL 94-V0** rated, self-extinguishing


899-018 RECTANGULAR FRONT PANEL MOUNT DUST COVER DIMENSIONS		
Part Number	A Ref.	B Ref.
899-018-09	.653 (16.59)	.233 (5.92)
899-018-15	.728 (18.49)	.233 (5.92)
899-018-21	.803 (20.40)	.233 (5.92)
899-018-25	.853 (21.67)	.233 (5.92)
899-018-31	.928 (23.57)	.233 (5.92)
899-018-37	1.003 (25.48)	.233 (5.92)
899-018-41	1.053 (26.75)	.233 (5.92)
899-018-51	1.178 (29.92)	.233 (5.92)
899-018-65	1.353 (34.37)	.233 (5.92)
899-018-69	1.403 (35.64)	.233 (5.92)
899-018-85	1.745 (44.32)	.258 (6.55)
899-018-91	1.820 (46.23)	.258 (6.55)

899-018 Rectangular Front Panel Mount Dust Covers



899-023 CIRCULAR DUST COVER DIMENSIONS			
Part Number	A	B	C
899-023-04	.250 (6.35)	.48 (12.19)	.49 (12.4 5)
899-023-05	.312 (7.92)	.56 (14.22)	.56 (14.22)
899-023-06	.375 (9.53)	.62 (15.75)	.51 (12.95)
899-023-08	.500 (12.70)	.73 (18.54)	.50 (12.70)
899-023-10	.625 (15.88)	.84 (21.34)	.50 (12.70)

899-023 Circular Dust Covers



899-023 CIRCULAR DUST COVER SIZE MATRIX				
Part Number	Shell Size			
	1	2	3	4
892-000	08	08	08	10
892-001	04	05	06	06
892-002	04	04	05	06
892-003	04	05	06	06
892-004	05	06	06	08
892-005	04	05	06	06
892-006	06	08	08	08
892-007	05	05	06	06
893-008	04	04	05	06
893-009	04	05	06	06
893-010	04	04	05	06
893-011	04	05	06	06