

SuperNine Series III PowerPlay Triple-Start
870H001 Swing-Arm Saddle Clamp

SUPER NINE SERIES III POWERPLAY TRIPLE-START





HOW TO ORDER				
Sample Part Number	870H001	XB	23	B
Basic Part Number	870H001 Swing-Arm Saddle Clamp for PowerPlay Connectors			
Material/Finish	XB = Composite, No Finish (Black) M = Aluminum, Electroless Nickel NF = Aluminum, Olive Drab Cadmium MT = Aluminum, Nickel-PTFR TZ = Aluminum, Tin-Zinc ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated			
Shell Size	11, 13, 15, 17, 19, 21, 23, 25			
Clamp Size	A = Standard Clamp B = Large Clamp			

MATERIAL/FINISH

- **Composite (Code XB)**
 - Coupling nut, body, arms, saddles: polyetherimide (PEI), unplated
 - Screws, washers, inserts: stainless steel/passivated
 - Anti-decoupling springs: thermoplastic
 - Clinch Nuts: stainless steel, silver plated
- **Aluminum (Codes M, MT, NF, TZ, ZR)**
 - Coupling nut, body, arms, saddles: aluminum
 - Screws, washers, inserts: stainless steel/passivated
 - Anti-decoupling springs: thermoplastic
 - Clinch Nuts: Codes M, MT, TZ and ZR: stainless steel, silver plated.
Code NF: stainless steel/ olive drab cadmium
- **Stainless Steel (Code Z1)**
 - Coupling nut, body, arms, saddles: SST
 - Screws, washers, inserts: stainless steel/passivated
 - Anti-decoupling springs: stainless steel
 - Clinch Nuts: stainless steel, silver plated

CLAMP DIMENSIONS							
<p>TYPE A STANDARD CLAMP</p>				<p>TYPE B LARGE CLAMP</p>			
Standard Clamp				Large Clamp			
Shell Size	L Max	M Min	N Ref.	Shell Size	P Max	R Min	S Ref.
11	1.05 (26.7)	.27 (6.9)	.310 (7.9)	11	1.20 (30.5)	.45 (11.4)	.422 (10.7)
13	1.20 (30.5)	.35 (8.9)	.422 (10.7)	13	1.45 (36.8)	.62 (15.7)	.637 (16.2)
15	1.30 (33.0)	.47 (11.9)	.538 (13.7)	15	1.54 (39.1)	.68 (17.3)	.707 (18.0)
17	1.44 (36.6)	.55 (14.0)	.590 (15.0)	17	1.60 (40.6)	.80 (20.3)	.759 (19.3)
19	1.56 (39.6)	.62 (15.7)	.660 (16.8)	19	1.73 (43.9)	.90 (22.9)	.841 (21.4)
21	1.69 (42.9)	.70 (17.8)	.744 (18.9)	21	1.95 (49.5)	1.05 (26.7)	.996 (25.3)
23	1.77 (45.0)	.78 (19.8)	.826 (21.0)	23	2.08 (52.8)	1.18 (30.0)	1.060 (26.9)
25	1.89 (48.0)	.85 (21.6)	.896 (22.8)	25	2.32 (58.9)	1.30 (33.0)	1.124 (28.5)

SuperNine Series III PowerPlay Triple-Start
870H001 Swing-Arm Saddle Clamp



Aluminum and SST Versions

Aluminum and stainless steel versions have round knurled coupling nuts.

SUPERNINE SERIES III POWERPLAY TRIPLE-START