

SERIES 253-020

AS81703 Series 3 Type Connectors



Contacts and Tools

Contacts and Tools					
Connector Part Number	Insert Arrangement	Contact P/N	Crimp Tool	Positioner	Ins / Ext Tools
253-020-06ME37-50PY	37-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06ME37-50SB	37-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06ME61-42PX	61-42	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
		M39029/4-111	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
		M39029/4-113	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-04
253-020-00ME61-42SX	61-42	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
		M39029/5-116	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
		M39029/5-118	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-04
253-020-06ME61-50PB	61-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06ME61-50SN	61-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06ME7-50PB	7-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06NF7-50SN	7-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06MT19-12SN	19-12	M39029/5-116	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-00ME19-12PN	19-12	M39029/4-111	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-00M12-50PN*	12-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME12-50SN	12-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00M19-50PN**	19-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME19-50SN	19-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00M19-7PN	19-7	M39029/4-113	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-04
253-020-00ME19-7SN	19-7	M39029/5-118	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-00ME12-6SN	12-6	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME27-50PN	27-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME27-50SN	27-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME27-5PN	27-5	M39029/4-111	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-06ME27-5SN	27-5	M39029/5-116	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-00ME3-50PN	3-50	M39029/4-110	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME3-50SN	3-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-00ME37-3SN-429	37-3	M39029/5-118	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-06-GSME61-50SN-GA	61-50	M39029/5-115	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-11
253-020-06ME27-2PN	27-2	M39029/4-111	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03
253-020-06ME27-2SN	27-2	M39029/5-116	809-136 (M22520/1-01)	859-032 (M22520/1-02)	M81969/14-03

CONTACTS

M39029/4-110	M39029/4-111	M39029/4-113	M39029/5-115	M39029/5-116	M39029/5-118

CRIMP TOOL

M22520/1-01

POSITIONER

M22520/1-02

INSERTION EXTRACTION TOOLS

M81969/14-11	M81969/14-03	M81969/14-04