

MIL-DTL-38999 Series I Type RF crimp contact tool cross reference

Shielded Contact Assembly Tools									
Contact P/N	Cable Accomodated		Gender	Size	Inner Contact		Cable Shield Hex		Insertion/ Removal Tool
					Tool	Positioner	Tool	Hex Die	
852-008 M39029/76	RG174, RG316, RG178, RG179		Pin	16	809-015 M22520/2-01	809-125 M22520/2-35	809-127 M22520/4-01	809-126 M22520/4-02	809-131 M81969/14-03
852-009 M39029/77	RG174, RG316, RG178, RG179		Skt	16	809-015 M22520/2-01	809-125 M22520/2-35	809-127 M22520/4-01	809-126 M22520/4-02	809-131 M81969/14-03
852-004 M39029/102	RG174, RG179, RG180, RG316		Pin	12	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01	809-130 M22520/5-03	809-132 M81969/14-04
852-005 M39029/103	RG174, RG179, RG180, RG316		Skt	12	809-015 M22520/2-01	859-123 K1457 (DMC)	809-129 M22520/5-01	809-130 M22520/5-03	809-132 M81969/14-04
852-006 M39029/59-366	RG180		Skt	8	809-015 M22520/2-01	859-050 M22520/2-31	809-129 M22520/5-01	859-051 M22520/5-05	859-049 M81969/14-12 Removal
852-007 M39029/60-367	RG180		Pin	8	809-015 M22520/2-01	859-050 M22520/2-31	809-129 M22520/5-01	859-051 M22520/5-05	859-049 M81969/14-12 Removal
852-082-XX	Dash: -01	PIC Cable: V78209	Pin	8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01	859-007 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	Times Microwave LMR-240-75		8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01	859-007 M22520/5-45	
	Dash: -03	Falmat: Deep Mini RG59 P/N: FM030115-4		8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01		
852-083-XX	Dash: -01	PIC Cable: V78209	Skt	8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01	859-007 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	Times Microwave LMR-240-75		8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01	859-007 M22520/5-45	
	Dash: -03	Falmat: Deep Mini RG59 P/N: FM030115-4		8	809-015 M22520/2-01	859-240 M22520/2-37	809-129 M22520/5-01		
852-030-XX	Dash: -01	M17/152-00001 (RG316DS),	Skt	8	Solder Contact		809-129 M22520/5-01	809-130 M22520/5-03	
	Dash: -02	M17/113-RG316		8			809-129 M22520/5-01	809-130 M22520/5-03	
	Dash: -03	M17/060-RG142; M17/12/-RG400		8			809-129 M22520/5-01	859-047 or 859-007 M22520/5-45	
	Dash: -04	M17/28-RG58		8			809-129 M22520/5-01	859-047 or 859-007 M22520/5-45	
852-031-XX	Dash: -01	M17/152-00001 (RG316DS),	Pin	8	Solder Contact		809-129 M22520/5-01	809-130 M22520/5-03	859-049 M81969/14-12 Removal
	Dash: -20	M17/113-RG316		8			809-129 M22520/5-01	809-130 M22520/5-03	
	Dash: -03	M17/060-RG142; M17/12/-RG400		8			809-129 M22520/5-01	859-047 or 859-007 M22520/5-45	
	Dash: -04	M17/28-RG58		8			809-129 M22520/5-01	859-047 or 859-007 M22520/5-45	

MIL-DTL-38999 Series I Type
RF crimp contact tool cross reference

CONTACTS AND TOOLS

Shielded Contact Assembly Tools									
Contact P/N	Cable Accomodated		Gender	Size	Inner Contact		Cable Shield Hex		Insertion/ Removal Tool
					Tool	Positioner	Tool	Hex Die	
852-042	LLSB-200, and LMR-195		Skt	8	Solder Contact		809-129 M22520/5-01	859-051 M22520/5-05	859-049 M81969/14-12 Removal
852-043	LLSB-200, and LMR-195		Pin	8	Solder Contact		809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
852-056 75 ohm	Dash: -01	V75268, V76261, V73263	Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	RG179		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	809-130 M22520/5-03	
852-057 75 ohm	Dash: -01	V75268, V76261, V73263	Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	RG179		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	809-130 M22520/5-03	
853-003 (M39029/113)	M17/176-00002		Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-048 M22520/5-105	859-049 M81969/14-12 Removal
853-004 (M39029/114)	M17/176-00002		Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-048 M22520/5-105	859-049 M81969/14-12 Removal
853-013	M17/176-00002		Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
853-014	M17/176-00002		Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
853-017	Raychem EPD 32263		Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
853-018	Raychem EPD 32263		Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
853-024-XX	Dash: -01	McDonnell Douglas ST5M1212-002	Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	Raychem 7726D0664							
853-025-XX	Dash: -01	Raychem 7726D0664	Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	McDonnell Douglas ST5M1212-002							

MIL-DTL-38999 Series I Type RF crimp contact tool cross reference

Shielded Contact Assembly Tools									
Contact P/N	Cable Accomodated		Gender	Size	Inner Contact		Cable Shield Hex		Insertion/ Removal Tool
					Tool	Positioner	Tool	Hex Die	
854-001-XX	Dash: -01	Tensolite NF26Q100	Pin	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	Tensolite NF24Q100, PIC E51424		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -03	Draka Fileca F 4704-6		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -04	Draka Fileca F 4704-4		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -05	Tensolite NF22Q100		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
854-002-XX	Dash: -01	Tensolite NF26Q100	Skt	8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	859-049 M81969/14-12 Removal
	Dash: -02	Tensolite NF24Q100, PIC E51424		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -03	Draka Fileca F 4704-6		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -04	Draka Fileca F 4704-4		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	
	Dash: -05	Tensolite NF22Q100		8	809-015 M22520/2-01	859-072 809-240 M22520/2-37	809-129 M22520/5-01	859-007 or 859-047 M22520/5-45	