

SPECIAL PURPOSE Pin Contacts




857-217-22-30

M39029/58-360 Type Size 22 Pin Contact with size 30 crimp barrel accommodation

SPECIAL PURPOSE



| HOW TO ORDER | | | |
|-----------------|-----------------------------|-----|-----|
| Sample Part No. | 857-217 | -22 | -30 |
| Product | 857-217-22-30 = Pin Contact | | |
| Contact Size | 22 | | |
| Wire Size, AWG | 30 | | |



| TABLE I - CRIMP TOOL SELECTOR | | | |
|-------------------------------|----|----|----|
| Wire | 26 | 28 | 30 |
| Selector | 5 | 4 | 3 |

MATERIAL / FINISH

- Copper alloy / gold plated per ASTM B 488, Type II, Code C, .000050 min thick over nickel per SAE AMS-QQ-N-290, Class 2, .000030 to .000150 thick.

NOTES

- Crimp tool data:
 - A) Crimp Frame - M22520/2-01 (Glenair p/n 809-015)
 - B) Positioner - M22520/2-09 (Glenair p/n 859-018)
 - C) Crimp tool selector: See Table I
 - D) Insertion/extraction tool - M81969/14-01 (Glenair p/n 859-020)
- Contact barrel accommodates 26 to 30 AWG