

SPECIAL PURPOSE CONTACTS


Bushings & Adapters



259-021 Large gauge wire barrel reducers for ITS or 5015 contacts



HOW TO ORDER				
Sample Part No.	259-021	Z3A	-16	-20
Product	259-021 = Crimp Reduction Sleeve			
Finish Code	Z3A = Silver Plate, .0001-.0003 Thick Z2A = Gold Plate, .00002 Min. Thick			
"From" Wire	Crimp Barrel Wire Size (AWG or mm2)			
"To" Wire	Wire Gauge Used (AWG or mm2)			



DIMENSIONS					
"Reduction Sleeve Part No. 259-021XXX-XX-XX"	From Wire Size	To Wire Size	ØA O.D.	ØB	"C Overall Length"
259-021XXX-20-26	20 AWG	26 AWG	0.046 (1.17)	0.070 (1.78)	0.146 (3.71)
259-021XXX-16-20	16 AWG	20 AWG	0.061 (1.55)	0.098 (2.49)	0.256 (6.50)
259-021XXX-16-22	16 AWG	22 AWG	0.061 (1.55)	0.098 (2.49)	0.256 (6.50)
259-021XXX-16-24	16 AWG	24 AWG	0.061 (1.55)	0.098 (2.49)	0.256 (6.50)
259-021XXX-16-26	16 AWG	26 AWG	0.061 (1.55)	0.098 (2.49)	0.256 (6.50)
259-021XXX-12-16	12 AWG	16 AWG	0.094 (2.39)	0.150 (3.81)	0.320 (8.13)
259-021XXX-12-18	12 AWG	18 AWG	0.094 (2.39)	0.150 (3.81)	0.320 (8.13)
259-021XXX-12-20	12 AWG	20 AWG	0.094 (2.39)	0.150 (3.81)	0.320 (8.13)
259-021XXX-8-6MM	8 AWG	6 mm2	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-10	8 AWG	10 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-12	8 AWG	12 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-14	8 AWG	14 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-16	8 AWG	16 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-18	8 AWG	18 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-8-20	8 AWG	20 AWG	0.174 (4.42)	0.273 (6.93)	0.465 (11.81)
259-021XXX-4-16MM	4 AWG	16 mm2	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-15MM	4 AWG	15 mm2	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-6	4 AWG	6 AWG	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-10MM	4 AWG	10 mm2	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-8	4 AWG	8 AWG	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-6MM	4 AWG	6 mm2	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-10	4 AWG	10 AWG	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-12	4 AWG	12 AWG	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-4-2.5MM	4 AWG	2.5 mm2	0.275 (6.99)	0.354 (8.99)	0.465 (11.81)
259-021XXX-0-50MM	0 AWG	50 mm2	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-35MM	0 AWG	35 mm2	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-2	0 AWG	2 AWG	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-25MM	0 AWG	25 mm2	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-16MM	0 AWG	16 mm2	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-4	0 AWG	4 AWG	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-6	0 AWG	6 AWG	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-10MM	0 AWG	10 mm2	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-0-8	0 AWG	8 AWG	0.440 (11.18)	0.531 (13.49)	0.535 (13.59)
259-021XXX-00-70MM	2/0 AWG	70 mm2	0.510 (12.95)	0.648 (16.46)	0.846 (21.49)
259-021XXX-00-50MM	2/0 AWG	50 mm2	0.522 (13.26)	0.650 (16.51)	0.827 (21.01)
259-021XXX-190-0000	190	4/0 AWG	0.781 (19.84)	0.925 (23.50)	0.906 (23.01)
259-021XXX-70MM-25MM	70 mm2	25 mm2	0.486 (12.34)	0.748 (19.00)	0.709 (18.01)
259-021XXX-70MM-50MM	70 mm2	50 mm2	0.509 (12.93)	0.689 (17.50)	0.886 (22.50)
259-021XXX-H9-2	IGE H9	2AWG	0.636 (16.15)	0.827 (21.01)	0.819 (20.80)