

Series 78 Rubber Covers

for Series 801 Mighty Mouse Connectors



809-191 Rubber Cover, Plug



809-191 covers fit Glenair Series 801 Mighty Mouse plug connectors. Rugged molded rubber "Mini-Bean" cover fits over the coupling nut and protects from dust and damage. Fungus-resistant, sulfur-free neoprene with nylon rope. Attachment choices include cable tie, slip knot or ring. Rings are stainless steel with non-reflective black coating. Splashproof, not submersible.

MATERIAL / FINISH

- Cover: black neoprene (standard), fungus resistant, sulfur-free
- Code C: conductive black neoprene, 100 ohms/sq. minimum
- Attachment cord: nylon, black
- Cable tie: black nylon with passivated SST screw and locknut
- Ring, eyelet: SST, black zinc cobalt
- Slip knot sleeve: copper/ black zinc cobalt



Shell Size	øA		øB	
	±.060 (1.5) In.	mm.	±.060 (1.5) In.	mm.
-05	.51	13.0	.70	17.8
-06	.57	14.5	.76	19.3
-07	.66	16.8	.85	21.6
-08	.72	18.3	.91	23.1
-09	.78	19.8	.97	24.6
-10	.85	21.6	1.03	26.2
-11	.89	22.6	1.08	27.4
-13	1.02	25.9	1.21	30.7
-16	1.21	30.7	1.40	35.6
-17	1.27	32.3	1.46	37.1
-19	1.38	35.1	1.56	39.6
-21	1.52	38.6	1.71	43.4

PART NUMBER

Base P/N	809-191	Plug Cover
Shell Size	-05 -06 -07 -08 -09 -10 -11 -13 -16 -17 -19 -21	
Attachment Type	<i>Omit for No Attachment</i> G Nylon Rope, .062 (1.6) diameter	
Attachment Length	<i>Length in 1 inch increments</i>	
Attachment Fitting	-00 No Fitting -SCS Slip Knot -WS Cable Tie <i>See Table 1 for Eyelet and Ring Attachment Fitting Codes</i>	
Material	<i>Omit for non-conductive black neoprene</i> C Conductive Black Neoprene (10 ⁵ Ω/square min)	

TABLE 1 ATTACHMENT FITTING

SLIP KNOT

Code **SCS**
Copper sleeve with black zinc cobalt finish. May be crimped after adjustment to permanently fix location.

CABLE TIE

Code **WS**
6/6 nylon cable tie with screw and locknut. 1.77 (45.0) max. wire bundle dia. -40 to +85 °C.

RING

Code	Ring I.D. ±.015 (0.4)	Code	Ring I.D. ±.015 (0.4)
-32	.265 (6.7)	-16	.885 (22.5)
-29	.315 (8.0)	-17	.896 (22.8)
-08	.385 (9.8)	-26	.950 (24.1)
-09	.445 (11.3)	-28	1.015 (25.8)
-10	.516 (13.1)	-19	1.070 (27.2)
-11	.570 (14.5)	-20	1.135 (28.8)
-12	.583 (14.8)	-22	1.210 (30.7)
-13	.635 (16.1)	-23	1.275 (32.4)
-14	.695 (17.7)	-30	1.380 (35.1)
-27	.766 (19.5)	-25	1.530 (38.9)

EYELET

Code	Eyelet I.D. ±.010 (0.3)
-01	.126 (3.2)
-02	.140 (3.6)
-03	.145 (3.7)
-04	.156 (4.0)
-05	.167 (4.2)
-06	.188 (4.8)
-07	.197 (5.0)