

# Series 78 Rubber Covers



for Series 805 Mighty Mouse Connectors

## 809-196 Rubber Cover, Receptacle



### MATERIAL / FINISH

Cover: black neoprene (standard), fungus resistant, sulfur-free  
 Code C: conductive black neoprene, 100 ohms/sq. minimum  
 Attachment cord: black nylon, black  
 Cable tie: black nylon with passivated SST screw and locknut  
 Ring, eyelet: SST, black zinc cobalt  
 Slip knot sleeve: copper/ black zinc cobalt



Shell Size	øA		øB	
	±.060 (1.5) In.	mm.	±.060 (1.5) In.	mm.
-08	.47	11.9	.66	16.8
-09	.53	13.5	.72	18.3
-10	.60	15.2	.78	19.8
-11	.66	16.8	.85	21.6
-12	.72	18.3	.91	23.1
-13	.78	19.8	.97	24.6
-15	.91	23.1	1.10	27.9
-18	1.10	27.9	1.28	32.5
-19	1.16	29.5	1.35	34.3
-21	1.28	32.5	1.47	37.3
-23	1.41	35.8	1.60	40.6

809-196 covers fit Glenair Series 805 Mighty Mouse receptacle connectors. Rugged molded rubber "Mini-Bean" cover protects equipment from dust and damage. Fungus-resistant, sulfur-free neoprene with nylon rope. Attachment choices include cable tie, slip knot or ring. Rings are stainless steel with non-reflective black coating. Splashproof, not submersible.

### PART NUMBER

	<b>809-196</b>	<b>-12</b>	<b>G</b>	<b>6</b>	<b>-02</b>	<b>C</b>
Base P/N	<b>809-196</b> Receptacle Cover					
Shell Size	<b>-08 -09 -10 -11 -12 -13 -15 -18 -19 -21 -23</b>					
Attachment Type	Omit for No Attachment <b>G</b> Nylon Rope, .062 (1.6) diameter					
Attachment Length	Length in 1 inch increments					
Attachment Fitting	<b>-00</b> No Fitting <b>-SCS</b> Slip Knot <b>-WS</b> Cable Tie See Table 1 for Eyelet and Ring Attachment Fitting Codes					
Material	Omit for non-conductive black neoprene <b>C</b> Conductive Black Neoprene (10 <sup>5</sup> Ω/square min)					

### TABLE 1 ATTACHMENT FITTING

**SLIP KNOT**

Code **SCS**  
 Copper sleeve with black zinc cobalt finish. May be crimped after adjustment to permanently fix location.

**CABLE TIE**

Code **WS**  
 6/6 nylon cable tie with screw and locknut. 1.77 (45.0) max. wire bundle dia. -40 to +85 °C.

**RING**

Code	Ring I.D. ±.015 (0.4)	Code	Ring I.D. ±.015 (0.4)
-32	.265 (6.7)	-19	.885 (22.5)
-29	.315 (8.0)	-26	.950 (24.1)
-14	.385 (9.8)	-28	1.015 (25.8)
-15	.445 (11.3)	-20	1.070 (27.2)
-33	.510 (13.0)	-21	1.135 (28.8)
-16	.570 (14.5)	-22	1.210 (30.7)
-17	.635 (16.1)	-23	1.275 (32.4)
-18	.695 (17.7)	-30	1.380 (35.1)
-27	.766 (19.5)	-25	1.530 (38.9)
-31	.820 (20.8)		

**EYELET**

Code	Eyelet I.D. ±.010 (0.3)
-01	.125 (3.2)
-02	.145 (3.7)
-04	.182 (4.6)
-06	.197 (5.0)