

447-329

Composite EMI/RFI Environmental Band-in-a-Can Backshell with Strain-Relief Clamp and Self-Locking Rotatable Coupling

CONNECTOR DESIGNATOR:

A	MIL-DTL-5015, -26482 Series II, and -83723 Series I and III
F	MIL-DTL-38999 Series I, II
L	MIL-DTL-38999 Series 1.5 (JN1003)
H	MIL-DTL-38999 Series III and IV
G	MIL-DTL-28840
U	DG123 and DG123A

SELF-LOCKING

ROTATABLE COUPLING

STANDARD PROFILE

Angle and Profile

S - Straight
W - 90° Elbow

Finish Symbol

(See Table III)

Band Option

Band supplied with **K** option
(Omit for none)

Product Series

447 - EMI/RFI Non-Environmental
Banding Backshells

Basic Part Number

Cable Entry

(See Table IV)

447

H

S

329

XM

19

20

C

K

S

Connector Designator

A, F, L, H, G and U

Connector Shell Size



(See Table II)

Strain Relief Style

C - Clamp
N - Nut

Slot Option


S - Pigtail
Termin. Slot
(Omit for none)



NOTES

1. Metric dimensions (mm) are in parenthesis and are for reference only.
2. Coupling nut supplied unplated.
3. See Table I in Intro for front-end dimensional details.

447-329
Composite EMI/RFI Environmental
Band-in-a-Can Backshell with Strain-Relief Clamp
and Self-Locking Rotatable Coupling



Composite
Backshells

A

TABLE II: CONNECTOR SHELL SIZE

Shell Size For Connector Designator*					E		F		G	Max Entry
A	F/L	H	G	U	±.06	(1.5)	±.09	(2.3)	Max	Dash No.**
08	08	09	—	—	.69	(17.5)	.88	(22.4)	1.31 (33.3)	10
10	10	11	—	08	.75	(19.1)	1.00	(25.4)	1.42 (36.1)	12
12	12	13	11	10	.81	(20.6)	1.13	(28.7)	1.57 (39.9)	14
14	14	15	13	12	.88	(22.4)	1.31	(33.3)	1.57 (39.9)	16
16	16	17	15	14	.94	(23.9)	1.38	(35.1)	1.64 (41.7)	20
18	18	19	17	16	.97	(24.6)	1.44	(36.6)	1.73 (43.9)	20
20	20	21	19	18	1.06	(26.9)	1.63	(41.4)	1.82 (46.2)	22
22	22	23	—	20	1.13	(28.7)	1.75	(44.5)	1.82 (46.2)	24
24	24	25	23	22	1.19	(30.2)	1.88	(47.8)	1.92 (48.8)	28
28	—	—	25	24	1.34	(34.0)	2.13	(54.1)	2.00 (50.8)	32

**Consult factory for additional entry sizes available.

TABLE III: FINISH

Symbol	Finish Description
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. 1000 Hour Grey™
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel

TABLE IV: CABLE ENTRY

Entry Code	H		J		Entry Dia.*		Cable Range **	
	±.06	(1.5)	±.06	(1.5)	±.03	(0.8)	Minimum	Maximum
10	.94	(23.9)	.80	(20.3)	.22	(5.6)	.13 (3.3)	.25 (6.4)
12	1.17	(29.7)	.93	(23.6)	.28	(7.1)	.25 (6.4)	.38 (9.7)
14	1.28	(32.5)	1.06	(26.9)	.34	(8.6)	.31 (7.9)	.44 (11.2)
16	1.41	(35.8)	1.22	(31.0)	.46	(11.7)	.50 (12.7)	.63 (15.9)
18	1.50	(38.1)	1.24	(31.5)	.55	(14.0)	.56 (14.2)	.69 (17.5)
20	1.56	(39.6)	1.37	(34.8)	.62	(15.7)	.63 (16.0)	.75 (19.1)
22	1.69	(42.9)	1.49	(37.8)	.70	(17.8)	.75 (19.1)	.88 (22.2)
24	1.81	(46.0)	1.62	(41.1)	.78	(19.8)	.88 (22.4)	1.00 (25.4)
28	1.91	(48.5)	1.68	(42.7)	.85	(21.6)	1.00 (25.4)	1.13 (28.6)
32	2.02	(51.3)	1.82	(46.2)	.95	(24.1)	1.13 (28.6)	1.25 (31.8)

* Entry diameter equals maximum wire bundle diameter.
 ** Cable range equals diameter of cable outer jacket.