

120-144 Annular Polymer-Core Convoluted Tubing




Outstanding mechanical wire protection and lubricity for non-EMI/RFI applications



Standard Black and Natural/Clear Annular Convoluted Tubing

Blue, Yellow, Red, Desert Tan, and Orange Annular Convoluted Tubing

How To Order




Dash No	A Inside Dia		B Outside Dia
	Min	Max	Max
06	.17 (4.3)	.19 (4.8)	.32 (8.1)
09	.24 (6.1)	.28 (7.1)	.42 (10.7)
12	.33 (8.4)	.37 (9.4)	.52 (13.2)
14	.40 (10.1)	.44 (11.2)	.59 (15.0)
16	.45 (11.4)	.50 (12.7)	.66 (16.8)
20	.57 (14.5)	.62 (15.7)	.77 (20.0)
24	.69 (17.5)	.75 (19.1)	.94 (23.9)
28	.81 (20.6)	.87 (22.1)	1.08 (27.4)
32	.93 (23.6)	1.00 (25.4)	1.20 (30.5)
40	1.18 (30.0)	1.25 (31.8)	1.44 (36.6)
48	1.43 (36.3)	1.50 (38.1)	1.71 (43.4)
52	1.56 (39.6)	1.63 (41.4)	1.85 (47.0)

Y	Kynar/Thermally stabilized
V	PVDF/Not thermally stabilized
S	G-FLEX Siltem/Medium duty

N	Natural/Clear
R	Red (available in PVDF only)
Y	Yellow (available in PVDF only)
BL	Blue (available in PVDF only)
TN	Desert Tan (available in PVDF only)
O	Orange (available in PVDF only)
Omit for standard black	

Dash No (I.D.)	Max. Length
09 (.281")	2000 ft.
12 (.375")	1500 ft.
16 (.5")	1000 ft.
20 (.625")	700 ft.
24 (.75")	500 ft.
32 (1")	300 ft.
40 (1.25")	200 ft.
48 (1.5")	200 ft.
52 (1.625")	200 ft.



Packaging

Long-length orders of conduit are subject to the practical limits of shipping box sizes. For example, the maximum length of 1/2 inch (dash 16) conduit that can fit in a standard shipping container is 1000 feet. Unless otherwise specified, Glenair standard practice is to ship optimal lengths of conduit material based on tubing diameter and box size. Consult factory for non-standard length or packaging requirements.