





713-394

Hat Trick System


Environmental Self-Locking Metal Backshell with Drop-In and Band Termination for Series 74 Helical Convolved Tubing

Easy-to-install Hat Trick convoluted tubing-to-bulkhead fitting, metal






How To Order



SYM S - STRAIGHT



Detail view with drop-in adapter extended for clarity. Area around and on the keys, conduit thread area and interfacial teeth free of PTFE coating



Material and Finish/Notes

- Adapters, Hex Nuts: Table II (See P/N development)
 - Anti-decoupling device: Corrosion-resistant material
 - O-Ring - Silicone/N.A. • Band - SST/Passivate • Shrink Boot - See individual drawing.
 - Assembly supplied with Micro-Band (600-057-1) for shield termination onto the drop-in adapter. Options B and C are for additional Standard Band to terminate overall shielding.
- *Internal surfaces coated with PTFE in area indicated, see P/N development.

713-394

Hat Trick System

Environmental Self-Locking Metal Backshell with Drop-In and
Band Termination for Series 74 Helical Convuluted TubingSeries 74
Helical Tubing

Table III: Connector Designator and Dimensions

Shell Size	A Thread			B Dia			C Dia Max	D Max	E Max	F Max	G Max
	Connector Designator A	Connector Designator F	Connector Designator H	A	F	H					
08/09	1/2-20 UNF	7/16-28 UNEF	M12 X 1.0-6H	.160 (4.1)	.138 (3.5)	.160 (4.1)	.94 (23.9)	1.000 (25.4)	1.220 (31.0)	1.158 (29.4)	1.380 (35.1)
10/11	5/8-24 UNEF	9/16-24 UNEF	M15 X 1.0-6H	.270 (6.9)	.248 (6.3)	.270 (6.9)	1.06 (26.9)	1.027 (26.1)	1.230 (31.2)	1.220 (31.0)	1.420 (36.1)
12/13	3/4-20 UNEF	11/16-24 UNEF	M18 X 1.0-6H	.390 (9.9)	.374 (9.5)	.390 (9.9)	1.17 (29.7)	1.027 (26.1)	1.230 (31.2)	1.220 (31.0)	1.420 (36.1)
14/15	7/8-20 UNEF	13/16-20 UNEF	M22 X 1.0-6H	.512 (13.0)	.455 (11.6)	.512 (13.0)	1.29 (32.8)	1.079 (27.4)	1.260 (32.0)	1.283 (32.6)	1.460 (37.1)
16/17	1-20 UNEF	15/16-20 UNEF	M25 X 1.0-6H	.610 (15.5)	.577 (14.7)	.627 (15.9)	1.42 (36.1)	1.105 (28.1)	1.260 (32.0)	1.345 (34.2)	1.500 (38.1)
18/19	1 1/16-18 UNEF	1 1/16-18 UNEF	M28 X 1.0-6H	.672 (17.1)	.672 (17.1)	.747 (19.0)	1.54 (39.1)	1.157 (29.4)	1.310 (33.3)	1.408 (35.8)	1.560 (39.6)
20/20	1 3/16-18 UNEF	1 3/16-18 UNEF	M31 X 1.0-6H	.797 (20.2)	.797 (20.2)	.891 (22.6)	1.67 (42.4)	1.183 (30.0)	1.360 (34.5)	1.470 (37.3)	1.640 (41.7)
22/23	1 5/16-18 UNEF	1 5/16-18 UNEF	M34 X 1.0-6H	.922 (23.4)	.922 (23.4)	.996 (25.3)	2.01 (51.1)	1.208 (30.7)	1.400 (35.6)	1.533 (38.9)	1.730 (43.9)
24/25	1 7/16-18 UNEF	1 7/16-18 UNEF	M37 X 1.0-6H	1.047 (26.6)	1.047 (26.6)	1.121 (28.5)	2.12 (53.8)	1.234 (31.3)	1.450 (36.8)	1.595 (40.5)	1.810 (46.0)

Table IV: Dash No. and Shrink Boot

Dash No.	H Conduit I.D. Nom	Ø J	Ø K	Shrink Boot Part Number
06	.188 (4.8)	.419 (10.6)	.481 (12.2)	770-001S103
09	.281 (7.1)	.513 (13.0)	.575 (14.6)	770-001S104
10	.312 (7.9)	.549 (13.9)	.611 (15.5)	770-001S104
12	.375 (9.5)	.609 (15.5)	.671 (17.0)	770-001S104
14	.437 (11.1)	.670 (17.0)	.732 (18.6)	770-001S104
16	.500 (12.7)	.749 (19.0)	.811 (20.6)	770-001S105
20	.625 (15.9)	.869 (22.1)	.931 (23.6)	770-001S106
24	.750 (19.0)	1.029 (26.1)	1.091 (27.7)	770-001S106
28	.875 (22.2)	1.172 (29.8)	1.234 (31.3)	770-001S107
32	1.000 (25.4)	1.320 (33.5)	1.382 (35.1)	770-001S107
40	1.250 (31.8)	1.664 (42.3)	1.726 (43.8)	770-001S108
48	1.500 (38.1)	1.957 (49.7)	2.019 (51.3)	770-001S108

Table II: Material/Finish

Table II: Material/Finish			
Sym	Material	Finish Description	
M	Aluminum Alloy	Electroless Nickel	
MT	Aluminum Alloy	Nickel-PTFE	
NF	Aluminum Alloy	Cad/O.D. Over Electroless Nickel (1,000 Hour Salt Spray)	
Z1	300 Series SST	Passivate	
ZN	Aluminum Alloy	Zinc Nickel/O.D. Over Electroless Nickel (1,000 Hour Salt Spray)	
Table II continued			
Sym	Material	Finish Description	Component
ZM	300 Series SST	Electroless Nickel	Adapters, Elbow
		Passivate	Coupling Nut
ZW	300 Series SST	Cad O.D. Over Electroless Nickel	Adapters, Elbow
		Cad Olive Drab	Coupling Nut

C