

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 790 High-Density

SERIES™
790
HD

790-070

Cable Plug with Solder Cup Contacts

- ◆ Solder cup pin contacts
- ◆ Non-environmental



Solder cup contacts. 790-070 cable plug has snap-in, rear-release solder cup socket contacts. Non-environmental. Contacts are supplied loose. Contacts can be removed with standard extraction tools. High-density size 23 contacts are on .075 inch (1.9mm) centers and accept AWG 22 or smaller wire. Machined aluminum shell has groove for attaching EMI banding backshell (799-015, sold separately). Optional gold-plated EMI spring.

- User-installed solder cup contacts
- 40 insert arrangements with up to 102 contacts
- Non-environmental, no wire grommet

INSERT ARRANGEMENTS






FULL COMPLEMENT OF CONTACTS	#8, #12 OR #16 CONTACTS PURCHASED SEPARATELY	No. of Contacts			
		#23	#16	#12	#8
A-5		5			
B-2P2	B-2W2		2		
B-9		9			
C-13		13			
D-15		15			
D-3P3	D-3W3		3		
D-7P2	D-7W2	5	2		
E-11P2	E-11W2	9	2		
E-19		19			
E-7P3	E-7W3	4	3		
F-14P3	F-14W3	11	3		
F-15P2	F-15W2	13	2		
F-23		23			
F-5P5	F-5W5		5		
G-13P2	G-13W2	11		2	
G-21P1	G-21W1	20		1	
G-3P3	G-3W3			3	
G-33		33			
H-10P4	H-10W4	6		4	
H-29P7	H-29W7	22	7		
H-36P2	H-36W2	34		2	
H-51P1	H-51W1	50		1	
H-54P2	H-54W2	52	2		
H-5P5	H-5W5			5	
H-66		66			
J-17P4	J-17W4	13	4		
J-25P2	J-25W2	23	2		
J-33		33			
J-7P7	J-7W7		7		
K-27P4	K-27W4	23	4		
K-35P2	K-35W2	33	2		
K-43		43			
K-9P9	K-9W9		9		
L-22P4	L-22W4	18		4	
L-48P2	L-48W2	46		2	
L-6P6	L-6W6			6	
L-78		78			
M-17P17	M-17W17		17		
M-102		102			
M-4P4	M-4W4				4

HOW TO ORDER

HOW TO ORDER

Sample Part Number		790-070S	D-3P3	E	M	S
Basic Part Number	790-070S	Cable Plug, Solder Cup Socket Contacts				
Shell Size-Insert Arr.	See <i>“Insert Arrangements”</i> Table					
EMI Spring	E EMI Spring <i>Shell finishes M and MT only</i> N No EMI Spring					
Shell Finish	M Electroless Nickel					
	MT Nickel / PTFE					
	N Olive Drab Cadmium					
	TZ Tin-Zinc					
	ZR Black Zinc-Nickel					
Hardware Option Table 1	N Thru-Hole <i>No hardware</i>					
	K Extended Jackscrews <i>Slot head male</i>					
	L Jackscrews <i>Socket head male</i>					
	P Female Jackposts					
	S Screwlocks <i>Socket head male</i>					
	T Extended Screwlocks <i>Slot head male</i>					

TABLE 1 HARDWARE OPTIONS

					
N	K	L	P	S	T
No Hardware Thru Mounting Holes	Extended Jackscrew Slot Head	Jackscrew Socket Head	Female Jackpost With Nut and Lockwasher	Screwlock Socket Head	Extended Screwlock Slot Head

Screwlocks allow connector to be plugged in before the screws are tightened. Jackscrews must be tightened in order to mate connector.

RATINGS

- Voltage (DWV): size 23 contacts 750 VAC, Size 8, 12 and 16: 1800 VAC
- Current: #23 5A, #16 13A, #12 23A, #8 46A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random
- Altitude immersion: *not rated*
- Ingress protection: *not rated*

CONSTRUCTION

- Socket Contacts: Copper alloy, gold over nickel finish. Stainless steel hood.
- Shell: Aluminum
- Insulators: High performance thermoplastic
- EMI spring: Stainless steel, gold plated
- Contact retaining clip: Beryllium copper, unplated
- Hardware: Stainless steel

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 790 High-Density



790-070

Cable Plug with Solder Cup Contacts

- ◆ Solder cup pin contacts
- ◆ Non-environmental



⚠ USER-INSTALLED SOLDER CUP CONTACTS ARE SUPPLIED LOOSE AND SNAP INTO CONNECTOR.

Shell Size	A Max		B ± .005 (0.1)		C Max		D Max		ø E ± .004 (0.1)		F Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
A	.785	19.9	.565	14.4	.335	8.5	.308	7.8	.092	2.3	.390	9.9
B	.935	23.7	.715	18.2	.485	12.3	.308	7.8	.092	2.3	.540	13.7
C	1.085	27.6	.865	22.0	.635	16.1	.308	7.8	.092	2.3	.690	17.5
D	1.185	30.1	.965	24.5	.735	18.7	.308	7.8	.092	2.3	.790	20.1
E	1.335	33.9	1.115	28.3	.885	22.5	.308	7.8	.092	2.3	.940	23.9
F	1.485	37.7	1.265	32.1	1.035	26.3	.308	7.8	.092	2.3	1.090	27.7
G	1.435	36.4	1.215	30.9	1.010	25.7	.395	10.0	.092	2.3	1.055	26.8
H	2.175	55.2	1.800	45.7	1.385	35.2	.410	10.4	.149	3.8	1.440	36.6
J	1.845	46.9	1.615	41.0	1.390	35.3	.308	7.8	.092	2.3	1.450	36.8
K	2.240	56.9	2.015	51.2	1.795	45.6	.308	7.8	.092	2.3	1.840	46.7
L	2.420	61.5	2.036	51.7	1.623	41.2	.410	10.4	.149	3.8	1.675	42.5
M	2.575	65.4	2.200	55.9	1.675	42.5	.470	11.9	.172	4.4	1.740	44.2

Application Note

Panel Mounting

For panel mounting, specify connector with Hardware Option N (thru-holes). Use rear panel mount jackpost **799-117**. See page **F-18** for jackpost ordering information, page **F-19** for panel cutout dimensions.

Application Note

EMI Banding Backshells



799-011

See page **F-24** for backshell ordering information




799-293

See page **F-28** for backshell ordering information


HARDWARE DIMENSIONS

Shell Size	Thread Size
A – G, J, K	#2-56
H, L	#4-40
M	#6-32




P

Female Jackpost with Hex Nut and Lockwasher




K T

Extended Jackscrew and Screwlock



L

Low Profile Jackscrew Socket Head



S

Low Profile Screwlock Socket Head