

MICRO-CRIMP RECTANGULAR CONNECTORS


Series 792 High-Speed




792-013

Float Mount Plug

- ◆ Crimp, rear-release
- ◆ Float mount blind mate
- ◆ Socket contacts




SECTION A-A



CONTACT POLARIZING KEY LOCATION


Series 792 size 8 contact cavities have a polarizing keyway. This keyway orients and aligns twinax, quadax and El Ochito® contacts. The connector keyway is rotated 45° from top dead center. This illustration shows the location of the polarizing key and the contact numbers when looking at the mating face of the plug (socket) connector.



Application Note

EMI Banding Backshell 799-183


See page F-37 for backshell ordering information.



Shell Size	A Max		B ± .005 (0.1)		C Max		D Max		E ± .005 (0.1)		F Max		G Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
A	2.317	58.85	1.075	27.31	.615	15.62	1.320	33.53	1.815	46.10	.754	19.15	.475	12.07
B	2.692	68.38	1.450	36.83	.990	25.15	1.695	43.06	2.190	55.63	.754	19.15	.475	12.07
C	3.067	77.90	1.825	46.36	1.365	34.67	2.070	52.58	2.565	65.15	.754	19.15	.475	12.07
D	3.442	87.43	2.200	55.88	1.740	44.20	2.445	62.10	2.940	74.68	.754	19.15	.475	12.07
E	3.817	96.95	2.575	65.41	2.115	53.72	2.820	71.63	3.315	84.20	.754	19.15	.475	12.07
F	3.817	96.95	2.575	65.41	2.115	53.72	2.820	71.63	3.315	84.20	1.129	28.68	.850	21.59


PANEL CUTOUT FOR 792-013 AND 792-014 FLOAT MOUNT CONNECTORS

Rear Mounting



Shell Size	A Basic		B ± .002 (0.06)		C		D		E	
	in	mm	in	mm	in	mm	in	mm	in	mm
A	1.815	46.10	1.075	27.31	.823	20.90	.412	10.46	.810	20.57
B	2.190	55.63	1.450	36.83	1.198	30.43	.599	15.21	1.185	30.10
C	2.565	65.15	1.825	46.36	1.573	39.95	.787	19.99	1.560	39.62
D	2.940	74.68	2.200	55.88	1.948	49.48	.974	24.74	1.935	49.15
E	3.315	84.20	2.575	65.41	2.323	59.00	1.162	29.51	2.310	58.67
F	3.315	84.20	2.575	65.41	2.323	59.00	1.162	29.51	2.323	59.00

Front Mounting



Shell Size	F Basic		G		H		J	
	in	mm	in	mm	in	mm	in	mm
A	1.815	46.10	1.465	37.21	.891	22.63	.621	15.77
B	2.190	55.63	1.840	46.74	1.266	32.16	.996	25.30
C	2.565	65.15	2.215	56.26	1.641	41.68	1.371	34.82
D	2.940	74.68	2.590	65.77	2.016	51.21	1.746	44.35
E	3.315	84.20	2.965	75.31	2.391	60.73	2.121	53.87
F	3.315	84.20	2.965	75.31	2.391	60.73	2.121	53.87