

OPTIMIZED
FOR USE WITH
MIL•STAR™
HIGH-PERFORMANCE HOOKUP WIRE AND CABLE




MIL-DTL-26482 Series 2 type rugged bayonet-coupling crimp-contact connectors



- For rugged military and industrial applications that require quick mate/demate three-point bayonet-lock coupling.
- Glenair 26482 Series 2-style connectors offer high-performance plating options unavailable in standard mil-spec parts including TZ Tin-Zinc, our recommended RoHS-material AMS2434 Type 2 qualified cadmium-compatible replacement, ZR black zinc-nickel, and Z1 passivated stainless steel.
- Complete range of tooled MIL-STD-1669 insert arrangements for size #20, #16, and #12 signal and power crimp, rear-release contacts. The Glenair solution offers three shell size 8 arrangements not available in the mil-spec version.
- Available integrated cable-shield banding porch option as well as PCB versions with rugged threaded standoffs for secure circuit board attachment.

Threaded connector
accessory interface and wire
sealing grommet standard.
Glenair signature integrated
band porch versions also
available.




Plug connectors



Narrow-flange
wall-mount receptacles



Wide-flange
wall-mount receptacles



Cable-connecting
receptacles



Jam-nut
receptacles

CRIMP-CONTACT MIL-DTL-26482 Series 2 Bayonet-Lock Connectors



Glenair signature and QPL designs (pending)

COUPLING TORQUE		
Shell Size	Torque	
	Maximum engagement and disengagement	Minimum disengagement
8	8 (.904 N-m)	1 (.113 N-m)
10	10 (1.13 N-m)	1 (.113 N-m)
12	14 (1.58 N-m)	2 (.226 N-m)
14	17 (1.92 N-m)	4 (.452 N-m)
16	23 (2.60 N-m)	4 (.452 N-m)
18	26 (2.94 N-m)	4 (.452 N-m)
20	31 (3.50 N-m)	6 (.678 N-m)
22	38 (4.29 N-m)	7 (.791 N-m)
24	38 (4.29 N-m)	7 (.791 N-m)

DIELECTRIC WITHSTANDING VOLTAGE		
Altitude (ft.)	Minimum Test Voltages, AC (RMS)	
	Service Rating I	Service Rating II
Sea Level	1,500	2,300
50,000	500	750
70,000	375	500
110,000	200	200

WORKING VOLTAGE, AC, RMS		
Condition	Service Rating I	Service Rating II
Sea Level	600	1,000
70,000 ft.	600	450

MATERIAL AND FINISH OPTIONS									
	Glenair code	Material	Finish	Finish Specification	Salt Spray Hrs.	Electrical Conductivity	Operating Temp. Range	RoHS Materials	Notes
Glenair COTS Code	AB	Marine Bronze	Unplated	AMS4640 alloy, unplated	1000	Conductive	-65° to +200°C	✓	Marine and geo-physical applications
	ME	Aluminum	Electroless Nickel	AMS-C-26074, Grade A; ASTM B733, SC 3	96	Conductive	-65° to +200°C	✓	Glenair's standard high-build electroless Nickel finish.
	NF	Aluminum	Cadmium, Olive Drab	AMS-QQ-P-416, Type II, Class 2, over electroless Nickel	500	Conductive	-65° to +175°C		Glenair's standard olive drab Cadmium finish.
	TZ	Aluminum	Tin-Zinc, Green-Gold	AMS2434, Type 2, over electroless Nickel	500	Conductive	-65° to +175°C	✓	Glenair's recommended Cadmium-compatible replacement.
	ZR	Aluminum	Zinc-Nickel, Black	ASTM B841, over electroless Nickel	500	Conductive	-65° to +175°C	✓	Glenair's standard black Zinc-Nickel finish.
	ZI	Stainless Steel	Passivate		48	Conductive	-55° to +200°C	✓	Passivated stainless steel

Consult Glenair for other material / finish options

MIL-SPEC CRIMP CONTACTS FOR GLENAIR SERIES 260-002 M26482 TYPE CONNECTORS

Glenair Series 260-002 MIL-DTL-26482 Series 2 type connectors are supplied with contacts (including spares), insertion / removal tool, and sealing plugs. Connectors may also be ordered without contacts. Additional contacts, insertion/removal tools, crimp tools, and positioners may be ordered using the part numbers on this page:

M39029/4-110 Size 20 pin contact	M39029/5-115 Size 20 socket contact	M39029/4-111 Size 16 pin contact	M39029/5-116 Size 16 socket contact	M39029/4-113 Size 12 pin contact	M39029/5-118 Size 12 socket contact